


DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



F





E

D

C

B

A



3 OBSOLETE

64	32	85,88	82,07	82,64	6-100103-4
60	30	80,80	76,99	77,56	6-100103-0
50	25	68,10	64,29	64,86	5-100103-0
44	22	60,48	56,67	57,24	4-100103-4
40	20	55,40	51,59	52,16	4-100103-0
34	17	47,78	43,97	44,54	3-100103-4
30	15	42,70	38,89	39,46	3-100103-0
26	13	37,62	33,81	34,38	2-100103-6
20	10	30,00	26,19	26,76	2-100103-0
16	8	24,92	21,11	21,68	1-100103-6
14	7	22,38	18,57	19,14	1-100103-4
10	5	17,30	13,49	14,06	1-100103-0
NR. OF CABLE POS.	NR. OF DUAL POS.	A	B	C	PARTNUMBER

NOTES:



ASSEMBLED WITH AMP-LATCH MIL-TYPE
RECEPT. CONN. (SYMMETRIC COVER)

2

250 PIECES PACKED IN A PLASTIC BAG.



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

GREY RAL 7032

GLASSFILLED NYLON

COLOR

MATERIAL

CUSTOMER DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

© COPYRIGHT 19 - BY

ALL INTERNATIONAL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION ,19 -



TE Connectivity

NAME

AMP-LATCH MIL-TYPE RECEPT.
CONN. STRAIN-RELIEF.

—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
C2	REVISED PER ECO-11-005140	RK	HMR	05APR11
LTR.	REVISION RECORD	DR.	CHK.	DATE
DR.: R.HOGEVEEN.	CHK.: R.VERSTIJNEN.	APP.: L.V.SOEST.	DWG.No.	REV.LTR.
DATE: 06-08-90	DATE: 08-08-90	DATE: 23-08-90	100103	C2

SHEET
1 OF 1

A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-100103-0](#)