








3 OBSOLETE

64	32	85,88	82,07	82,64	6-100103-4
60	30	80,80	76,99	77,56	6-100103-0
50	25	68,10	64,29	64,86	5-100103-0
44	22	60,48	56,67	57,24	4-100103-4
40	20	55,40	51,59	52,16	4-100103-0
34	17	47,78	43,97	44,54	3-100103-4
30	15	42,70	38,89	39,46	3-100103-0
26	13	37,62	33,81	34,38	2-100103-6
20	10	30,00	26,19	26,76	2-100103-0
16	8	24,92	21,11	21,68	1-100103-6
14	7	22,38	18,57	19,14	1-100103-4
10	5	17,30	13,49	14,06	1-100103-0
NR. OF CABLE POS.	NR. OF DUAL POS.	A	B	C	PARTNUMBER

NOTES:

- 1 ASSEMBLED WITH AMP-LATCH MIL-TYPE
RECEPT. CONN. (SYMMETRIC COVER)
- 2 250 PIECES PACKED IN A PLASTIC BAG.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

GREY RAL 7032	GLASSFILLED NYLON
COLOR	MATERIAL

—	—	—	—	—	CUSTOMER DRAWING		FOR REFERENCE ONLY WILL NOT BE UPDATED	
—	—	—	—	—	© COPYRIGHT 19 — BY			
—	—	—	—	—	ALL INTERNATIONAL RIGHTS RESERVED.			
—	—	—	—	—	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION —,19 —			
—	—	—	—	—	TE Connectivity			
—	—	—	—	—	NAME			
C2	REVISED PER ECO-11-005140	RK	HMR	05APR11	AMP-LATCH MIL-TYPE RECEPT. CONN. STRAIN-RELIEF.			
LTR.	REVISION RECORD		DR.	CHK.	DATE			A3
DR.: R.HOGEVEEN.	CHK.: R.VERSTIJNEN.		APP.: L.V.SOEST.	DWG.No.		REV.LTR.	SHEET	
DATE: 06-08-90	DATE: 08-08-90		DATE: 23-08-90	100103		C2	1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-100103-6](#)