






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		D2	SHEET 2 DRAFTING ERROR CORRECTION	10NOV2011	A.S	M.W



SECTION A-A
=====



NOTES:

- 1 DRAWING SHOWS CODING KEY 6-100525-3 WITH CODE NUMBER 3568 AS AN EXAMPLE. REINFORCED CODING KEYS ARE DESIGNED FOR THE 8 ROW CONNECTOR SYSTEM, BUT FIT THE 5 ROW CONNECTOR SYSTEM AS WELL.
- 2 DRAWING SHOWS CODING KEY 2-100525-4 WITH CODE NUMBER 1368 AS AN EXAMPLE.
- 3 MATERIAL: GLASSFILLED POLYAMIDE 6.6.; COLOUR: SEE TABLE.
- 4 EACH CODING KEY HAS FOUR BLOCKING PINS AND FOUR CAVITIES. THE NUMBERS ON TOP OF THE BLOCKING PINS FORM THE FOUR-FIGURE IDENTIFICATION NUMBER (ASCENDING).
- 5 PARTNUMBER MATCHING FEMALE CODING KEY, FOR REFERENCE ONLY.
- 6 1 INSERTION TOOL INCLUDED PER 500 CODING KEYS.

6-100526-3	PASTEL ORANGE	2003	3568	1	6-100525-3
6-100526-1	STEEL BLUE	5011	3478		6-100525-1
5-100526-9	SLATE GREY	7015	3467		5-100525-9
5-100526-6	CADMIUM YELLOW	1021	3456		5-100525-6
5-100526-4	RESADA GREEN	6011	2578		5-100525-4
3-100526-2	BRILLIANT BLUE	5007	1567		3-100525-2
100526-9	STRAWBERRY RED	3018	1248		100525-9
100526-3	NUT BROWN	8011	1236		100525-3
FEMALE KEY	COLOUR	RAL NR.	ID. NUMBER	4	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.IRUREN 03-FEB-98	TE Connectivity			
		CHK D.IRUREN 03-FEB-98				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± °	APVD F.v. KONINGSBRUGGE	NAME			
		PRODUCT SPEC	Z-PACK 2mm HM MALE CODING KEY			
		APPLICATION SPEC	—			
MATERIAL	FINISH	WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=100525	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 of 2	REV D2	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

—

—

SEE SHEET 1

—

—

—

8,9

7,2

A

6,5

5,75

1,2 TYP.

A

3

1

8

6

SECTION A-A

=====

10,8

7,9

3,15

POLARIZING PIN.

0,8

2,5

0,4

100525

6-100526-9

OCHER YELLOW

1024

4678

6-100525-9

6-100526-4

RASPBERRY RED

3027

3578

6-100525-4

5-100526-3

OCEAN BLUE

5020

2568

5-100525-3

5-100526-2

EMERALD GREEN

6001

2567

5-100525-2

4-100526-9

YELLOW ORANGE

2000

2467

4-100525-9

4-100526-8

HEATHER VIOLET

4003

2458

4-100525-8

4-100526-4

COPPER BROWN

8004

2368

4-100525-4

4-100526-3

STONE GREY

7030

2367

4-100525-3

3-100526-7

PURPLE RED

3004

2346

3-100525-7

3-100526-5

SALMON PINK

3022

1678

3-100525-5

3-100526-4

RED LILAC

4001

1578

3-100525-4

2-100526-7

LIGHT IVORY

1015

1457

2-100525-7

2-100526-6

PASTEL GREEN

6019

1456

2-100525-6

2-100526-4

YELLOW GREEN

6018

1368

2-100525-4

2-100526-0

BLUE LILAC

4005

1356

2-100525-0

1-100526-8

PIGEON BLUE

5014

1347

1-100525-8

1-100526-4

OLIVE YELLOW

1020

1268

1-100525-4

1-100526-3

CEMENT GREY

7033

1267

1-100525-3

1-100526-2

LIGHT GREEN

6027

1258

1-100525-2

100526-8

PURE ORANGE

2004

1247

100525-8

100526-5

ULTRAMARINE BLUE

5002

1238

100525-5

100526-2

GREEN BROWN

8000

1235

100525-2

FEMALE KEY

COLOUR

RAL NR.

ID. NUMBER

PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

D.TRUREN

D.TRUREN

F.v. KONINGSBRUGGE

—

—

—

—

—

—

MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.3

1 PLC ± 0.3

2 PLC ± 0.3

3 PLC ± 0.3

4 PLC ± 0.3

ANGLES ± —

FINISH

—

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

03-FEB-98

03-FEB-98

—

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

Z-PACK 2mm HM

MALE CODING KEY

—

A2

00779

100525

1:1

SHEET

2 of 2

REV

D2

1471-9

(3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-100525-0](#)