




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.RINGLY	11JUN85		 TE Connectivity Ltd.						
DIMENSIONS: INCHES		CHK D.DUPLER	11JUN85		ASSEMBLY, MOD II,HEADER,SINGLE ROW .100 C/L, RIGHT ANGLE,WITH .025 SQ POST —						
 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		APVD —	—							NAME	
		PRODUCT SPEC —									
		APPLICATION SPEC —									
MATERIAL RETARDANT THERMOPLASTIC, COLOR=BLACK — POSTS=PHOS BRONZE		FINISH SEE TABLE	WEIGHT —	A2		CAGE CODE 00779	DRAWING NO C-102203		RESTRICTED TO —		
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 2		REV W1			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

		910	OBSOLETE	8	1.720	1.640	1.500	15	16	4-102203-0
SUPERSEDED BY 8-102203-4				8	.420	.340	.200	2	3 3	3-102203-9
		910	OBSOLETE	8	1.020	.940	.800	8	9	3-102203-8
SUPERSEDED BY 5-102203-1				8	.520	.440	.300	3	4	3-102203-7
		610	OBSOLETE	7	.820	.740	.600	6	7	3-102203-6
SUPERSEDED BY 103361-8				7	1.120	1.040	.900	9	4 10	3-102203-5
				7	.420	.340	.200	2	3 3	3-102203-4
			OBSOLETE	7	3.720	3.640	3.500	35	36	3-102203-3
			OBSOLETE	7	3.620	3.540	3.400	34	35	3-102203-2
			OBSOLETE	7	3.520	3.440	3.300	33	34	3-102203-1
			OBSOLETE	7	3.420	3.340	3.200	32	33	3-102203-0
			OBSOLETE	7	3.320	3.240	3.100	31	32	2-102203-9
			OBSOLETE	7	3.220	3.140	3.000	30	31	2-102203-8
			OBSOLETE	7	3.120	3.040	2.900	29	30	2-102203-7
			OBSOLETE	7	3.020	2.940	2.800	28	29	2-102203-6
			OBSOLETE	7	2.920	2.840	2.700	27	28	2-102203-5
			OBSOLETE	7	2.820	2.740	2.600	26	27	2-102203-4
			OBSOLETE	7	2.720	2.640	2.500	25	26	2-102203-3
		10	OBSOLETE	7	2.620	2.540	2.400	24	25	2-102203-2
				7	2.520	2.440	2.300	23	24	2-102203-1
		10	OBSOLETE	7	2.420	2.340	2.200	22	23	2-102203-0
		10		7	2.320	2.240	2.100	21	22	1-102203-9
		10	OBSOLETE	7	2.220	2.140	2.000	20	21	1-102203-8
				7	2.120	2.040	1.900	19	20	1-102203-7
		10	OBSOLETE	7	2.020	1.940	1.800	18	19	1-102203-6
				7	1.920	1.840	1.700	17	18	1-102203-5
		10	OBSOLETE	7	1.820	1.740	1.600	16	17	1-102203-4
				7	1.720	1.640	1.500	15	16	1-102203-3
				7	1.620	1.540	1.400	14	15	1-102203-2
				7	1.520	1.440	1.300	13	14	1-102203-1
				7	1.420	1.340	1.200	12	13	1-102203-0
				7	1.320	1.240	1.100	11	12	102203-9
				7	1.220	1.140	1.000	10	11	102203-8
				7	1.120	1.040	.900	9	10	102203-7
		10		7	1.020	.940	.800	8	9	102203-6
				7	.920	.840	.700	7	8	102203-5
				7	.820	.740	.600	6	7	102203-4
				7	.720	.640	.500	5	6	102203-3
				7	.620	.540	.400	4	5	102203-2
				7	.520	.440	.300	3	4	102203-1
				FINISH	D	C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.RINGLY 11JUN85		 TE Connectivity Ltd.	
		CHK D.DUPLER 11JUN85			
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, MOD II,HEADER,SINGLE ROW .100 C/L, RIGHT ANGLE,WITH .025 SQ POST —	
		APVD —			
		PRODUCT SPEC —			
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		APPLICATION SPEC —		SIZE A2	
		MATERIAL —		FINISH SEE TABLE	
		WEIGHT —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-102203	
				RESTRICTED TO —	
				SCALE 1:1	
				SHEET 2 OF 2	
				REV W1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-102203-9](#)