




D

C

B

A



RECOMMENDED HOLE LAYOUT

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- .000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL.
- .000100-.000200 BRIGHT TIN OVER .000050 NICKEL.
- PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK. POSTS: COPPER ALLOY
- .000100-.000200 MATTE TIN OVER .000050 NICKEL.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

		3.984	3.900	39	40	9-103323-0
OBSOLETE		3.884	3.800	38	39	8-103328-9
OBSOLETE		3.784	3.700	37	38	8-103328-8
OBSOLETE		3.684	3.600	36	37	8-103328-7
		3.584	3.500	35	36	8-103328-6
OBSOLETE		3.484	3.400	34	35	8-103328-5
OBSOLETE		3.384	3.300	33	34	8-103328-4
OBSOLETE		3.284	3.200	32	33	8-103328-3
OBSOLETE		3.184	3.100	31	32	8-103328-2
OBSOLETE		3.084	3.000	30	31	8-103328-1
OBSOLETE		2.984	2.900	29	30	8-103328-0
OBSOLETE		2.884	2.800	28	29	7-103323-9
OBSOLETE		2.784	2.700	27	28	7-103323-8
OBSOLETE		2.684	2.600	26	27	7-103323-7
OBSOLETE		2.584	2.500	25	26	7-103323-6
OBSOLETE		2.484	2.400	24	25	7-103323-5
OBSOLETE		2.384	2.300	23	24	7-103323-4
OBSOLETE		2.284	2.200	22	23	7-103323-3
OBSOLETE		2.184	2.100	21	22	7-103323-2
OBSOLETE		2.084	2.000	20	21	7-103323-1
		1.984	1.900	19	20	7-103323-0
OBSOLETE		1.884	1.800	18	19	6-103323-9
OBSOLETE		1.784	1.700	17	18	6-103323-8
OBSOLETE		1.684	1.600	16	17	6-103323-7
OBSOLETE		1.584	1.500	15	16	6-103323-6
OBSOLETE		1.484	1.400	14	15	6-103323-5
OBSOLETE		1.384	1.300	13	14	6-103323-4
OBSOLETE		1.284	1.200	12	13	6-103323-3
OBSOLETE		1.184	1.100	11	12	6-103323-2
OBSOLETE		1.084	1.000	10	11	6-103323-1
		.984	.900	9	10	6-103323-0
OBSOLETE		.884	.800	8	9	5-103323-9
OBSOLETE		.784	.700	7	8	5-103323-8
OBSOLETE		.684	.600	6	7	5-103323-7
OBSOLETE		.584	.500	5	6	5-103323-6
		.484	.400	4	5	5-103323-5
		.384	.300	3	4	5-103323-4
OBSOLETE		.284	.200	2	3	5-103323-3
OBSOLETE		.184	.100	1	2	5-103323-2
OBSOLETE		.084	—	—	1	5-103323-1
PLATING	C	B	A	NO OF POSN	PART NUMBER	

			.184	.100	1	2	4-103323-2
			3.984	3.900	39	40	4-103323-1
			3.984	3.900	39	40	4-103323-0
	OBSOLETE		3.884	3.800	38	39	3-103323-9
	OBSOLETE		3.784	3.700	37	38	3-103323-8
	OBSOLETE		3.684	3.600	36	37	3-103323-7
	SUPERSEDED		3.584	3.500	35	36	3-103323-6
	OBSOLETE		3.484	3.400	34	35	3-103323-5
	OBSOLETE		3.384	3.300	33	34	3-103323-4
	OBSOLETE		3.284	3.200	32	33	3-103323-3
	OBSOLETE		3.184	3.100	31	32	3-103323-2
	OBSOLETE		3.084	3.000	30	31	3-103323-1
	OBSOLETE		2.984	2.900	29	30	3-103323-0
	OBSOLETE		2.884	2.800	28	29	2-103323-9
	OBSOLETE		2.784	2.700	27	28	2-103323-8
	OBSOLETE		2.684	2.600	26	27	2-103323-7
	OBSOLETE		2.584	2.500	25	26	2-103323-6
	OBSOLETE		2.484	2.400	24	25	2-103323-5
	OBSOLETE		2.384	2.300	23	24	2-103323-4
	OBSOLETE		2.284	2.200	22	23	2-103323-3
	OBSOLETE		2.184	2.100	21	22	2-103323-2
	OBSOLETE		2.084	2.000	20	21	2-103323-1
			1.984	1.900	19	20	2-103323-0
	OBSOLETE		1.884	1.800	18	19	1-103323-9
	OBSOLETE		1.784	1.700	17	18	1-103323-8
	OBSOLETE		1.684	1.600	16	17	1-103323-7
			1.584	1.500	15	16	1-103323-6
	OBSOLETE		1.484	1.400	14	15	1-103323-5
	OBSOLETE		1.384	1.300	13	14	1-103323-4
	OBSOLETE		1.284	1.200	12	13	1-103323-3
	OBSOLETE		1.184	1.100	11	12	1-103323-2
	OBSOLETE		1.084	1.000	10	11	1-103323-1
			.984	.900	9	10	1-103323-0
			.884	.800	8	9	103323-9
	OBSOLETE		.784	.700	7	8	103323-8
			.684	.600	6	7	103323-7
			.584	.500	5	6	103323-6
	SUPERSEDED		.484	.400	4	5	103323-5
	SUPERSEDED		.384	.300	3	4	103323-4
			.284	.200	2	3	103323-3
			.184	.100	1	2	103323-2
	OBSOLETE		.084			1	103323-1
	PLATING	C	B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

6

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

FINISH SEE TABLE

DWN J.MARTINELLI

CHK JOHN KNITTLE

APVD B.FLINCHBAUGH

WEIGHT -

CUSTOMER DRAWING

160CT92

23NOV92

23NOV92

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100 , RIGHT ANGLE, WITH .025 SQUARE POSTS

A100779

103323

SCALE 4:1

SHEET 1 OF 1

REV L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-103323-4](#)