




 OBSOLETE		2	2.59	1.295	1-103653-1	12	6-103946-1
		2	2.39	1.195	1-103653-0	11	6-103946-0
		2	2.19	1.095	103653-9	10	5-103946-9
		2	1.99	.995	103653-8	9	5-103946-8
		2	1.79	.895	103653-7	8	5-103946-7
		3	2.39	.795	103653-6	7	5-103946-6
		2	1.39	.695	103653-5	6	5-103946-5
		4	2.38	.595	103653-4	5	5-103946-4
		4	1.98	.495	103653-3	4	5-103946-3
		5	1.98	.395	103653-2	3	5-103946-2
		8	2.36	.295	103653-1	2	5-103946-1
		8	2.36	.295	103653-1	2	1-103946-2
 OBSOLETE		2	2.59	1.295	1-103653-1	12	1-103946-1
		2	2.39	1.195	1-103653-0	11	4-103946-0
		2	2.19	1.095	103653-9	10	103946-9
		2	1.99	.995	103653-8	9	103946-8
		2	1.79	.895	103653-7	8	103946-7
		3	2.39	.795	103653-6	7	103946-6
		2	1.39	.695	103653-5	6	103946-5
		4	2.38	.595	103653-4	5	103946-4
		4	1.98	.495	103653-3	4	103946-3
		5	1.98	.395	103653-2	3	103946-2
		8	2.36	.295	103653-1	2	103946-1
	PLATING		B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP

- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 26JUL00 CHK K WRIGHT 26JUL00 APVD K WRIGHT 26JUL00		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± - ± -		NAME SHROUDED PIN ASSY, AMPMODU MTE, SINGLE ROW, .100 CL, POLARIZED, W/ LATCH WINDOWS, FOR NO 22-NO 26 AWG WIRE SIZE, STRIP FORM	
MATERIAL 		FINISH SEE TABLE		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-103946	
				RESTRICTED TO -	
				SCALE 4:1 SHEET 1 OF 1 REV K2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103946-1](#)