



111	12	2	2.40	1.198	1-104257-1	12	6-103956-1
	12	2	2.20	1.098	1-104257-0	1 1	6-103956-0
	12	2	2.00	.998	104257-9	10	5-103956-9
	12	2	1.80	.898	104257-8	9	5-103956-8
	12	2	1.60	.798	104257-7	8	5-103956-7
	12	2	1.40	.698	104257-6	7	5-103956-6
	12	4	2.39	.598	104257-5	6	5-103956-5
	12	4	1.99	.498	104257-4	5	5-103956-4
	12	5	1.99	.398	104257-3	4	5-103956-3
	12	8	2.40	.298	104257-2	3	5-103956-2
	12	10	2.00	.198	104257-1	2	5-103956-1
	10	2	1.40	.698	104257-6	7	1-103956-8
	10	2	1.60	.798	104257-7	8	1-103956-7
	10	4	2.39	.598	104257-5	6	1-103956-6
	10	4	1.99	.498	104257-4	5	1-103956-5
	10	5	1.99	.398	104257-3	4	1-103956-4
	10	8	2.40	.298	104257-2	3	1-103956-3
	10	10	2.00	.198	104257-1	2	1-103956-2
	9	2	2.40	1.198	1-104257-1	12	1-103956-1
	9	2	2.20	1.098	1-104257-0	1 1	1-103956-0
	9	2	2.00	.998	104257-9	10	103956-9
	9	2	1.80	.898	104257-8	9	103956-8
	9	2	1.60	.798	104257-7	8	103956-7
	9	2	1.40	.698	104257-6	7	103956-6
	9	4	2.39	.598	104257-5	6	103956-5
	9	4	1.99	.498	104257-4	5	103956-4
	9	5	1.99	.398	104257-3	4	103956-3
	9	8	2.40	.298	104257-2	3	103956-2
9	10	2.00	.198	104257-1	2	103956-1	

PLATING				B		A		HOUSING PART NUMBER		NO OF POSN		ASSEMBLY PART NUMBER ON STRIP							
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN LA MAYER 11-4-86		TE Connectivity Ltd.													
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK P de Jong 11-12-86		NAME													
		0 PLC ± -		APVD P de Jong 11-12-86		RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 C/L, LATCHED & POLARIZED, FOR #22-#26 AWG WIRE SIZE, STRIP FORM													
		1 PLC ± -		PRODUCT SPEC															
		2 PLC ± .02		108-25034															
		3 PLC ± .005		APPLICATION SPEC															
4 PLC ± -		4 PLC ± -		114-25026		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO							
MATERIAL		FINISH		WEIGHT		A2		00779		C=103956		-							
HOUSING:		SEE TABLE		CUSTOMER DRAWING										SCALE 4:1		SHEET 1 OF 1		REV P2	

- 1471-9 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103956-0](#)