




LOC		DIST		REVISIONS			
AD		00		P	LTR	DESCRIPTION	DATE
					M2	REVISED PER ECO-11-004917	11MAR11
							DWN
							APVD
							RK
							HMR

13	12	2	2.40	1.198	1-104257-1	12	6-103959-1
		2	2.20	1.098	1-104257-0	1 1	6-103959-0
		2	2.00	.998	104257-9	10	5-103959-9
		2	1.80	.898	104257-8	9	5-103959-8
		2	1.60	.798	104257-7	8	5-103959-7
		2	1.40	.698	104257-6	7	5-103959-6
		4	2.39	.598	104257-5	6	5-103959-5
		4	1.99	.498	104257-4	5	5-103959-4
		5	1.99	.398	104257-3	4	5-103959-3
		8	2.40	.298	104257-2	3	5-103959-2
13	12	10	2.00	.198	104257-1	2	5-103959-1
		5	1.99	.398	104257-3	4	1-103959-3
		4	1.99	.498	104257-4	5	1-103959-2
		2	2.40	1.198	1-104257-1	12	1-103959-1
		2	2.20	1.098	1-104257-0	1 1	1-103959-0
		2	2.00	.998	104257-9	10	103959-9
		2	1.80	.898	104257-8	9	103959-8
		2	1.60	.798	104257-7	8	103959-7
		2	1.40	.698	104257-6	7	103959-6
		4	2.39	.598	104257-5	6	103959-5
13	9	4	1.99	.498	104257-4	5	103959-4
		5	1.99	.398	104257-3	4	103959-3
		8	2.40	.298	104257-2	3	103959-2
		10	2.00	.198	104257-1	2	103959-1
		PLATING					
		6	B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP
		THIS DRAWING IS A CONTROLLED DOCUMENT.					
		DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN L A MAYER 11-4-86	
				0 PLC ± -		CHK P de Jong 11-12-86	
				1 PLC ± -		APVD P de Jong 11-12-86	
				2 PLC ± .02		NAME	
				3 PLC ± .005		RCPT ASSY, AMPMODU MTE, SINGLE	
13	9	4 PLC ± -		114-25026		ROW .100 C/L, LATCHED AND POLARIZED	
		ANGLES ± -		114-25026		FOR #26-#30 AWG WIRE SIZE, STRIP FORM	
		FINISH		WEIGHT -		SIZE	
		SEE TABLE		CUSTOMER DRAWING		CAGE CODE	
						DRAWING NO	
						RESTRICTED TO	
						A2 00779 C=103959	
						SCALE	
						4:1	
						SHEET	
13	9					1 of 1	
						REV	
						M2	

103959

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-103959-4](#)