










- 1 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION WITH DATUM 
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 4 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 5 MATERIAL: HOUSING- FLAME RETARDANT THERMOPLASTIC, COLOR- BLACK
POST- PHOS BRONZE
- 6 FINISH: POST- .000015 GOLD IN CONTACT AREA,
.000100-.000200 MATTE TIN-LEAD ON SOLDERTAIL,
ALL OVER .000050 NICKEL
- 7 FINISH: POST- .000015 GOLD IN CONTACT AREA,
.000100-.000200 MATTE TIN ON SOLDERTAIL,
ALL OVER .000050 NICKEL
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△ ₈	OBSOLETE	△ ₇	1.900	1.600	16	34	6-104317-8		
	OBSOLETE		2.000	1.700	17	36	6-104317-7		
			1.000	.700	7	16	6-104317-6		
			2.300	2.000	20	42	6-104317-5		
	OBSOLETE		2.700	2.400	24	50	6-104317-4		
	OBSOLETE		2.600	2.300	23	48	6-104317-3		
	OBSOLETE		2.200	1.900	19	40	6-104317-2		
			1.800	1.500	15	32	6-104317-1		
			1.700	1.400	14	30	6-104317-0		
			1.500	1.200	12	26	5-104317-9		
△ ₈	OBSOLETE	△ ₇	1.400	1.100	11	24	5-104317-8		
			1.300	1.000	10	22	5-104317-7		
			1.200	.900	9	20	5-104317-6		
			1.100	.800	8	18	5-104317-5		
	△ ₈		OBSOLETE	△ ₇	.900	.600	6	14	5-104317-4
					.800	.500	5	12	5-104317-3
					.700	.400	4	10	5-104317-2
					.500	.200	2	6	5-104317-1
					.600	.300	3	8	△ ₄ 1-104317-9
			OBSOLETE		1.900	1.600	16	34	1-104317-8
OBSOLETE		2.000	1.700		17	36	1-104317-7		
		1.000	.700		7	16	1-104317-6		
		2.300	2.000		20	42	1-104317-5		
△ ₈		OBSOLETE	△ ₇		2.700	2.400	24	50	1-104317-4
	OBSOLETE	2.600		2.300	23	48	1-104317-3		
		2.200		1.900	19	40	1-104317-2		
		1.800		1.500	15	32	1-104317-1		
	△ ₈	OBSOLETE		△ ₇	1.700	1.400	14	30	1-104317-0
					1.500	1.200	12	26	104317-9
					1.400	1.100	11	24	104317-8
					1.300	1.000	10	22	104317-7
					1.200	.900	9	20	104317-6
					1.100	.800	8	18	104317-5
△ ₈		OBSOLETE	△ ₇		.900	.600	6	14	104317-4
					.800	.500	5	12	104317-3
					.700	.400	4	10	104317-2
					.500	.200	2	6	104317-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN H MOLL 10-19-87		 ETE		TE Connectivity	
		CHK R FEIDT 10-19-87					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME	HDR ASSY, MOD II, SHROUDED 4 SIDES, DBL ROW, W/OUT .100X.100 CL, W/ .025 SQ POSTS	
		0 PLC ± —		PRODUCT SPEC		RESTRICTED TO	
		1 PLC ± —		—			
		2 PLC ± .005		APPLICATION SPEC			
3 PLC ± —		4 PLC ± —		SIZE		CAGE CODE	DRAWING NO
ANGLES FINISH		WEIGHT		A1	00779	 104317	REV
MATERIAL	SEE TABLE	CUSTOMER DRAWING		SCALE		SHEET	OF
				4:1		1	K3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-104317-1](#)