











- 1 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION WITH DATUM -P-
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 4 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 5 MATERIAL: HOUSING- FLAME RETARDANT THERMOPLASTIC, COLOR- BLACK
POST- PHOS BRONZE
- 6 FINISH: POST- .000015 GOLD IN CONTACT AREA,
.000100-.000200 MATTE TIN-LEAD ON SOLDERTAIL,
ALL OVER .000050 NICKEL
- 7 FINISH: POST- .000015 GOLD IN CONTACT AREA,
.000100-.000200 MATTE TIN ON SOLDERTAIL,
ALL OVER .000050 NICKEL
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△ ₈	OBSOLETE	△ ₇	1.900	1.600	16	34	6-104317-8
	OBSOLETE		2.000	1.700	17	36	6-104317-7
			1.000	.700	7	16	6-104317-6
			2.300	2.000	20	42	6-104317-5
	△ ₈ OBSOLETE		2.700	2.400	24	50	6-104317-4
	△ ₈ OBSOLETE		2.600	2.300	23	48	6-104317-3
	△ ₈ OBSOLETE		2.200	1.900	19	40	6-104317-2
			1.800	1.500	15	32	6-104317-1
			1.700	1.400	14	30	6-104317-0
			1.500	1.200	12	26	5-104317-9
△ ₈	OBSOLETE	△ ₆	1.400	1.100	11	24	5-104317-8
			1.300	1.000	10	22	5-104317-7
			1.200	.900	9	20	5-104317-6
			1.100	.800	8	18	5-104317-5
	△ ₈ OBSOLETE		.900	.600	6	14	5-104317-4
			.800	.500	5	12	5-104317-3
			.700	.400	4	10	5-104317-2
			.500	.200	2	6	5-104317-1
	△ ₈ OBSOLETE		.600	.300	3	8	△ ₄ 1-104317-9
	△ ₈ OBSOLETE		1.900	1.600	16	34	1-104317-8
△ ₈	OBSOLETE	△ ₅	2.000	1.700	17	36	1-104317-7
			1.000	.700	7	16	1-104317-6
			2.300	2.000	20	42	1-104317-5
	△ ₈ OBSOLETE		2.700	2.400	24	50	1-104317-4
	△ ₈ OBSOLETE		2.600	2.300	23	48	1-104317-3
			2.200	1.900	19	40	1-104317-2
			1.800	1.500	15	32	1-104317-1
			1.700	1.400	14	30	1-104317-0
			1.500	1.200	12	26	104317-9
			1.400	1.100	11	24	104317-8
△ ₈		△ ₄	1.300	1.000	10	22	104317-7
			1.200	.900	9	20	104317-6
			1.100	.800	8	18	104317-5
	△ ₈ OBSOLETE		.900	.600	6	14	104317-4
			.800	.500	5	12	104317-3
			.700	.400	4	10	104317-2
			.500	.200	2	6	104317-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN H MOLL 10-19-87		 TE Connectivity			
		CHK R FEIDT 10-19-87					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD —		HDR ASSY, MOD II, SHROUDED 4 SIDES, DBL ROW, WET .100X.100 CL, W/ .025 SQ POSTS			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL		FINISH		WEIGHT			
		SEE TABLE		—			
CUSTOMER DRAWING				SIZE A1	CAGE CODE 00779	DRAWING NO  104317	RESTRICTED TO —
				SCALE 4:1	SHEET 1 OF 1	REV K3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-104317-9](#)