




1. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
2. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
3. RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.
4. $\varnothing .020\text{M}$ FOR KINKED TAILS
5. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	3.984	3.900	39	40	2-104346-7
	3.484	3.400	34	35	2-104346-6
	2.984	2.900	29	30	2-104346-5
	2.584	2.500	25	26	2-104346-4
	2.484	2.400	24	25	2-104346-3
	2.384	2.300	23	24	2-104346-2
	2.284	2.200	22	23	2-104346-1
	2.184	2.100	21	22	2-104346-0
OBSOLETE	2.084	2.000	20	21	1-104346-9
	1.984	1.900	19	20	1-104346-8
	1.884	1.800	18	19	1-104346-7
	1.784	1.700	17	18	1-104346-6
	1.684	1.600	16	17	1-104346-5
	1.584	1.500	15	16	1-104346-4
	1.484	1.400	14	15	1-104346-3
	1.384	1.300	13	14	1-104346-2
OBSOLETE	1.284	1.200	12	13	1-104346-1
	1.184	1.100	11	12	1-104346-0
	1.084	1.000	10	11	104346-9
	.984	.900	9	10	104346-8
	.884	.800	8	9	104346-7
	.784	.700	7	8	104346-6
	.684	.600	6	7	104346-5
	.584	.500	5	6	104346-4
OBSOLETE	.484	.400	4	5	104346-3
	.384	.300	3	4	104346-2
	.284	.200	2	3	104346-1
	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 08FEB88	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK R. FEIDT 08FEB88				
		APVD R. FEIDT 08FEB88	NAME			
		PRODUCT SPEC	HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100 CL, VERT, .025 SQ POSTS, WITH RETENTION FEATURE			
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POSTS: PHOSPHOR BRONZE		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	A2	-	C=104346	-
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH POSTS: .000100-.000200 MATTE TIN-LEAD, ALL OVER .000050 NICKEL			CUSTOMER DRAWING			SCALE 4:1 SHEET 1 of 1 REV K1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104346-2](#)