



LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					N	REVISED PER ECO-14-000066	26JUN2014	NK	MM

- 1 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 4 RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.
- 5 FOR 2 POSITION PART ONLY, THE NOTED DIM. IS .184.
- 6 $\varnothing .020 \text{ (M)}$ FOR KINKED TAILS.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



SUPERSEDED BY 6-146269-5	7 OBSOLETE	3.084	3.000	30	62	2-104350-1
	OBSOLETE	3.984	3.900	39	80	2-104350-0
		2.984	2.900	29	60	1-104350-9
	7	2.484	2.400	24	50	1-104350-8
	OBSOLETE	1.984	1.900	19	40	1-104350-7
		1.684	1.600	16	34	1-104350-6
		1.484	1.400	14	30	1-104350-5
		1.384	1.300	13	28	1-104350-4
		1.284	1.200	12	26	1-104350-3
	7	1.184	1.100	11	24	1-104350-2
	OBSOLETE	1.084	1.000	10	22	1-104350-1
		.984	.900	9	20	1-104350-0
		.884	.800	8	18	104350-9
		.784	.700	7	16	104350-8
		.684	.600	6	14	104350-7
		.584	.500	5	12	104350-6
		.484	.400	4	10	104350-5
		.384	.300	3	8	104350-4
		.284	.200	2	6	104350-3
		.184	.100	1	4	104350-2
		.084	—	—	2	104350-1
C		B	A	NO OF POSN	ASSEMBLY PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 08FEB88	 TE Connectivity					
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK R. FEIDT 08FEB88	NAME					
		APVD R. FEIDT 08FEB88	HEADER ASSY, MOD II, BREAKAWAY, DBL ROW, .100X.100 CL., VERT, .025 SQ POSTS, WITH RETENTION FEATURE					
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	APPLICATION SPEC	SIZE		RESTRICTED TO			
			A1		-			
MATERIAL HOUSING FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POST: COPPER ALLOY		FINISH POST: .000030 GOLD IN CONTACT AREA .000100-.000250 MATTE TIN LEAD ON SOLDER TAIL, ALL OVER .000250 NICKEL		WEIGHT		CUSTOMER DRAWING		
		SCALE 4:1		SHEET 1 OF 1		REV N		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104350-5](#)