



D

C

B

A



- 1 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 4 PART INDICATED IS PACKAGED IN SINGLE TUBES.
- 5 RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.
- 6 FOR 2 POSITION PART ONLY, THE NOTED DIMENSION IS  $.184$
- 7  $\phi .020$  FOR KINKED TAILS
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

|                          |            |   |       |       |            |                      |            |
|--------------------------|------------|---|-------|-------|------------|----------------------|------------|
| SUPERSEDED BY 104351-8   | 8 OBSOLETE |   | 1.784 | 1.700 | 17         | 36                   | 2-104351-3 |
|                          |            | 4 | .784  | .700  | 7          | 16                   | 2-104351-2 |
| SUPERSEDED BY 1-104351-3 |            | 4 | 1.284 | 1.200 | 12         | 26                   | 2-104351-1 |
|                          |            |   | 3.984 | 3.900 | 39         | 80                   | 2-104351-0 |
| 8 OBSOLETE               |            |   | 2.984 | 2.900 | 29         | 60                   | 1-104351-9 |
|                          |            |   | 2.484 | 2.400 | 24         | 50                   | 1-104351-8 |
| OBSOLETE                 |            |   | 1.984 | 1.900 | 19         | 40                   | 1-104351-7 |
|                          | 8          |   | 1.684 | 1.600 | 16         | 34                   | 1-104351-6 |
| SUPERSEDED BY 6-146268-4 |            |   | 1.484 | 1.400 | 14         | 30                   | 1-104351-5 |
|                          |            |   | 1.384 | 1.300 | 13         | 28                   | 1-104351-4 |
| SUPERSEDED BY 6-146268-1 |            |   | 1.284 | 1.200 | 12         | 26                   | 1-104351-3 |
|                          |            |   | 1.184 | 1.100 | 11         | 24                   | 1-104351-2 |
| 8 OBSOLETE               |            |   | 1.084 | 1.000 | 10         | 22                   | 1-104351-1 |
|                          |            |   | .984  | .900  | 9          | 20                   | 1-104351-0 |
| 8 OBSOLETE               |            |   | .884  | .800  | 8          | 18                   | 104351-9   |
|                          |            |   | .784  | .700  | 7          | 16                   | 104351-8   |
|                          |            |   | .684  | .600  | 6          | 14                   | 104351-7   |
|                          |            |   | .584  | .500  | 5          | 12                   | 104351-6   |
|                          |            |   | .484  | .400  | 4          | 10                   | 104351-5   |
|                          |            |   | .384  | .300  | 3          | 8                    | 104351-4   |
|                          |            |   | .284  | .200  | 2          | 6                    | 104351-3   |
|                          |            |   | .184  | .100  | 1          | 4                    | 104351-2   |
|                          |            |   | .084  | —     | —          | 2                    | 104351-1   |
|                          | REMARKS    | C | B     | A     | NO OF POSN | ASSEMBLY PART NUMBER |            |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-104351-0](#)