






THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 28JUN88 CHK R FEIDT 28JUN88		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		APVD R FEIDT 28JUN88 NAME HEADER ASSY, MOD II, BREAKAWAY, DBL ROW, .100X.100 CL, VERT, .025 SQ POSTS, WITH RETENTION FEATURE	
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POST: COPPER ALLOY		FINISH POST: .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL		WEIGHT — SIZE A2 CAGE CODE 00779 DRAWING NO C-104432 RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1 REV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104432-4](#)