






1. .000100 MIN BRIGHT TIN—LEAD OVER .000050 MIN NICKEL ON ENTIRE CONTACT
2. .000050 MIN NICKEL ON ENTIRE CONTACT; .000015 MIN GOLD ON CONTACT AREA; .000050 MIN BRIGHT TIN—LEAD ON AREA M.
3. .000050 MIN NICKEL ON ENTIRE CONTACT; .000030 MIN GOLD ON CONTACT AREA; .000050 MIN BRIGHT TIN—LEAD ON AREA M.
4. LOOSE PIECE CUT—OFF DIMENSION.
5. .000015 MIN GOLD ON CONTACT AREA, .000050 MIN TIN ON AREA M, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
6. .000030 MIN GOLD ON CONTACT AREA, .000050 MIN TIN ON AREA M, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
8. .000100 MIN TIN OVER .000050 MIN NICKEL ON ENTIRE CONTACT

	LOOSE PIECE		REF	5-104481-6
	STRIP			5-104481-2
	LOOSE PIECE		REF	1-104481-3
	LOOSE PIECE		REF	1-104481-2
	STRIP			1-104481-1
	STRIP			1-104481-0
OBSOLETE	LOOSE PIECE			104481-9
	LOOSE PIECE		REF	104481-8
	LOOSE PIECE		REF	104481-7
	LOOSE PIECE		REF	104481-6
OBSOLETE	STRIP			104481-5
	STRIP			104481-4
	STRIP			104481-3
	STRIP			104481-2
	REMARKS		FINISH	PART NO

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104481-7](#)