

	DESIGNED FOR USE WITH RG-196/U	REVISIONS				
	CABLE ENTRY DIAMETER MINIMUM	REV	DESCRIPTION	DATE	APPROVED	
	HOUSING	.037	02 <sub>2</sub>	REVISED	K.L. 7-26-96 8/1/96	<i>[Signature]</i>
	CONTACT	.012	B	PER EC 0U20-0116-01-02	10/29/01	C. Hoang
	FERRULE	.098				

HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	GOLD PLATE PER MIL-G-45204
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BRASS PER ASTM-B-16, HALF HARD	GOLD PLATE PER MIL-G-45204
RETAINING RING	BERYLLIUM COPPER PER ASTM-B-194, ALLOY C17200, CONDITION H	N/A
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
SHRINK TUBING	HEAT SHRINKABLE POLYOLEFIN COMPOUND MIL-I-23053/4	N/A
FERRULE	COPPER OR BRASS ALLOY ROCKWELL F65 MAXIMUM	GOLD PLATE PER MIL-G-45204

COMPONENT		MATERIAL		FINISH	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		DRAWN BY DJC 2-22-68		DATE	
FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		CHECKED BY PRB 2-22-68		AMP Incorporated	
		APPD BY PRB 2-22-68		140 Fourth Avenue Waltham, MA 02451-7599	
These drawings and speci- fications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale o f item(s) without written permission.		USE ASSY PROCEDURE  NO. A.P. 40-001 408-08250		TITLE "OSMM" STRAIGHT CABLE PLUG CRIMP ATTACHMENT	
		SIZE B	CODE IDENT NO. 26805	4031-7196-00	REV 02 <sub>2</sub>
		SCALE 8:1	RG-196/U	SHEET 1 OF 1	

.XXX = in  
XX.X = mm (REF)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1059057-1](#)