



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₂	REVISED	PATLAN 9-09-98	<i>[Signature]</i> 4/19/99
B	PER EC 0U20-0116-01-03	13NOV01	<i>C. Hoang</i> 13NOV01

HOUSING COUPLING NUT SLIDE ASS'Y	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	ELECTRO-POLISHED
HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35
CONTACT EXT.	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
CENTER CONTACT	BRASS PER ASTM-B-16, HALF HARD	GOLD PLATE PER MIL-G-45204

COMPONENT			MATERIAL			FINISH										
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES			DRAWN BY		DATE	<div>AMP Incorporated</div> <div>140 Fourth Avenue</div> <div>Waltham, MA 02451-7599</div>										
			CD		6-30-82											
			CHECKED BY													
			PCV		7-01-82											
FRAC.	DEC.	ANGLES	APP'D BY			<div>AMP</div>										
± 1/64	±.020	± 1°	DRG		7-02-82											
These drawings and specifications are the property of AMP Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.			USE ASS'Y PROCEDURE			TITLE			7mm PRECISION TO "OSP" PLUG ADAPTER							
						NO. A.P. <u>N/A</u>			SIZE		CODE IDENT NO.		REV			
									B		26805		4581-2700-00		01 ₂	
									SCALE		4:1		SHEET 1 OF 1			

NOTES:
1. CAPTURED CENTER CONTACT
2. SPECIFICATION;
FREQ. RANGE: DC TO 18.0 GHz
MAX VSWR 1.03 + .004f(GHz)

.XXX = in
XX.X = mm (REF)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1059713-1](#)