









Contact arrangement / view from termination side




Contact arrangement / view from termination side



Contact arrangement / view from termination side



Contact arrangement / view from termination side




NOTES:


- 1 SUITABLE CRIMP CONTACTS: SERIES HE/HA
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,2 MM
- 2 SUITABLE HOOD SIZE 5; 7; 9; 11: SERIES HA; HD
SUITABLE INSERTION AND EXTRACTION TOOL:
SCREWDRIVER 0,5x3 DIN 5264
- 3 Strip length: Screw connection 10mm
Spring clamp connection 10mm Crimp connection 7.5mm
- 4 STANDARDS:
DIN EN 61984; DIN EN 60664-1

- 5 PACKAGING:
5 SETS IN A CARTON, PRE-MOUNTED
- 6 SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 300 PIECES
- 7 SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 150 PIECES
- 8 SPECIAL PACKAGING: AIS
PACKAGING UNIT: 250 PIECES
- 9 SPECIAL PACKAGING: WIELAND
PACKAGING UNIT: 100 PIECES

Panel cut-out for contact insert when used without housing



Assembling instruction



 DISTANCE FOR SAFETY
CONTACT MARKING MAX. 24 mm

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1103417-8](#)