



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AA4	REVISED PER ECR-18-005503	30MAY2018	BDA	SG

- 1 MATING CONN P/N: □-1123722-□
- 2 APPLICABLE P.C.B LAYOUT: SEE FIG. 1
- 3 APPLICABLE P.C.B THICKNESS: 1.60
- 4 SKETCHES SHOW NO PINS MISSING.

- 6 PIN: POST TIN OVER BRASS
- 7 HOUSING: PBT, 30% GLASS, UL94-V0.
- 8 ○ : WITH PIN,
X : WITHOUT PIN.

- 10 SUPERSEDED BY 1744489-2.
- 11 SUPERSEDED BY 1744489-4.
- 12 SUPERSEDED BY 1744489-5.
- 13 SUPERSEDED BY 1744489-6.
- 14 SUPERSEDED BY 1744489-7.
- 15 SUPERSEDED BY 1744489-8.
- 16 SUPERSEDED BY 1744489-9.
- 17 SUPERSEDED BY 1-1744489-0.
- 18 SUPERSEDED BY 1-1744489-1.

VALUES FOR UL 61800-5-1				
Flam	RTIe deg C	HWI	HAI	CTI
V0	130	PLC 2	PLC 4	PLC 2_UL746



2 FIG.1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01	TE Connectivity		
DIMENSIONS: mm		CHK M.SHINDO 13MAR'01			
		APVD Y.KASHIWA 13MAR'01	NAME 3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY		
		PRODUCT SPEC 108-5609			
MATERIAL SEE TABLE		FINISH SEE TABLE	SIZE A2	CAGE CODE 00779	DRAWING NO C=1123723
		WEIGHT	RESTRICTED TO —		
		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 2	REV AA4

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By - ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

											27.72	29.12	31.62	NATURAL	8	7-1123723-8
														GREEN		6-1123723-8
														BLACK		5-1123723-8
														RED		4-1123723-8
														BLUE		3-1123723-8
														YELLOW		2-1123723-8
														NATURAL		1-1123723-8
														NATURAL		7-1123723-7
											GREEN	6-1123723-7				
											BLACK	5-1123723-7				
											RED	4-1123723-7				
											BLUE	3-1123723-7				
											YELLOW	2-1123723-7				
											NATURAL	1-1123723-7				
											NATURAL	7-1123723-6				
											GREEN	6-1123723-6				
											BLACK	5-1123723-6				
											RED	4-1123723-6				
											BLUE	3-1123723-6				
											YELLOW	2-1123723-6				
											NATURAL	1-1123723-6				
											NATURAL	7-1123723-5				
											GREEN	6-1123723-5				
											BLACK	5-1123723-5				
											RED	4-1123723-5				
											BLUE	3-1123723-5				
											YELLOW	2-1123723-5				
											NATURAL	1-1123723-5				
											NATURAL	7-1123723-4				
											GREEN	6-1123723-4				
											BLACK	5-1123723-4				
											RED	4-1123723-4				
											BLUE	3-1123723-4				
											YELLOW	2-1123723-4				
											NATURAL	1-1123723-4				
											NATURAL	7-1123723-3				
											GREEN	6-1123723-3				
											BLACK	5-1123723-3				
											RED	4-1123723-3				
											BLUE	3-1123723-3				
											YELLOW	2-1123723-3				
											NATURAL	1-1123723-3				
											NATURAL	7-1123723-2				
											GREEN	6-1123723-2				
											BLACK	5-1123723-2				
											RED	4-1123723-2				
											BLUE	3-1123723-2				
											YELLOW	2-1123723-2				
											NATURAL	1-1123723-2				
1	2	3	4	5	6	7	8	9	10	11	"C"	"B"REF	"A"REF	COLOR	POS	ASS'Y P/N
PIN POSITION											DIMENSION			COLOR	POS	ASS'Y P/N

○	○	○	○	○	○	○	○	○	○	○	39.60	41.00	43.50	NATURAL	11	18 8-1123723-1		
○	○	○	○	○	○	○	○	○	○	○				6-1123723-1				
○	○	○	○	○	○	○	○	○	○	○				5-1123723-1				
○	○	○	○	○	○	○	○	○	○	○				4-1123723-1				
○	○	○	○	○	○	○	○	○	○	○				3-1123723-1				
○	○	○	○	○	○	○	○	○	○	○				2-1123723-1				
○	○	○	○	○	○	○	○	○	○	○				1-1123723-1				
○	○	○	○	○	○	○	○	○	○	△				NATURAL		17 7-1123723-0		
○	○	○	○	○	○	○	○	○	○	△	GREEN	6-1123723-0						
○	○	○	○	○	○	○	○	○	○	△	BLACK	5-1123723-0						
○	○	○	○	○	○	○	○	○	○	△	RED	4-1123723-0						
○	○	○	○	○	○	○	○	○	○	△	BLUE	3-1123723-0						
○	○	○	○	○	○	○	○	○	○	△	YELLOW	2-1123723-0						
○	○	○	○	○	○	○	○	○	○	△	NATURAL	1-1123723-0						
○	○	○	○	○	○	○	○	○	○	△	31.68	33.08	35.58	NATURAL	16 7-1123723-9			
○	X	○	○	○	X	○	○	○	○	○	39.60	41.00	43.50	NATURAL	7-1123723-1			
○	○	○	○	○	○	○	○	○	△	△	31.68	33.08	35.58	GREEN	6-1123723-9			
○	○	○	○	○	○	○	○	○	△	△				BLACK	5-1123723-9			
○	○	○	○	○	○	○	○	○	△	△				RED	4-1123723-9			
○	○	○	○	○	○	○	○	○	△	△				BLUE	3-1123723-9			
○	○	○	○	○	○	○	○	○	△	△				YELLOW	2-1123723-9			
○	○	○	○	○	○	○	○	○	△	△				NATURAL	1-1123723-9			
○	○	○	○	○	○	○	○	○	△	△								
1	2	3	4	5	6	7	8	9	10	11	"C"	"B"	REF	"A"	REF	COLOR	POS	ASS'Y P/N
PIN POSITION 8											DIMENSION				COLOR	POS	ASS'Y P/N	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01 CHK M.SHINDO 13MAR'01 APVD Y.KASHIWA 13MAR'01		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.50 2 PLC ± 0.30 3 PLC ± 4 PLC ± ANGLES ±		NAME 3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY	
		PRODUCT SPEC 108-5609		SIZE A2	
MATERIAL SEE TABLE		APPLICATION SPEC —		CAGE CODE 00779	
FINISH SEE TABLE		WEIGHT —		DRAWING NO C-1123723	
CUSTOMER DRAWING		SCALE 5:1		SHEET 2 OF 2	
REV AA4		RESTRICTED TO —		REV AA4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-1123723-4](#)