

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
J	ZDI		C	REVISED		30MAR2015	K.R N.Y

注 記

1 材料：ハウジング：ガラス入り熱可塑性ポリエステル樹脂（94V-0），色：黒

2 ハウジング全面にテフロン塗装のこと

NOTES

1 MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
,POLYESTER(94V-0),COLOR:BLACK

2 TO COAT ALL SURFACE OF HOUSING WITH TEFLON

CIRCUIT NO.
回路番号

ROW ID MARK
列番号

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差

10 ≥ : ±0.3
>10 : ±0.35
30 ≥ : ±0.4
>30 : ±0.4
ANGLE : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

DWN
K.IKEDA
7/DEC/'98

CHK
N.MATSUBARA
7/DEC/'98

APVD
I.HASEGAWA
7/DEC/'98

PRODUCT SPEC
108-5619

APPLICATION SPEC
114-5258

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

2列 タブ ハウジング フリーハンギング タイプ
DOUBLE ROW TAB (FREE HANGING)
DYNAMIC D2100D

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1318115

RESTRICTED TO
-

SCALE
2:1

SHEET
1 OF 1

REV
C

				KEYING:Z 3-1318115-6				
<div>OBSOLETE</div>	<div>△</div>	22.5	27.7	11.5	11.5	9	20	5-1318115-9
	-	22.5	27.7	11.5	11.5	9	20	2-1318115-9
<div>OBSOLETE</div>	<div>△</div>	22.5	27.7	11.5	11.5	9	20	1-1318115-9
	-	12.5	17.7	11.5	11.5	5	12	5-1318115-6
<div>OBSOLETE</div>	<div>△</div>	12.5	17.7	11.5	11.5	5	12	3-1318115-6
	-	12.5	17.7	11.5	11.5	5	12	2-1318115-6
<div>OBSOLETE</div>	<div>△</div>	12.5	17.7	11.5	11.5	5	12	1-1318115-6
	-	7.5	12.7	4	4	3	8	5-1318115-4
<div>OBSOLETE</div>	<div>△</div>	7.5	12.7	4	4	3	8	2-1318115-4
	-	7.5	12.7	4	4	3	8	1-1318115-4
<div>OBSOLETE</div>	<div>△</div>	5	10.2	4	4	2	6	5-1318115-3
	-	5	10.2	4	4	2	6	2-1318115-3
<div>OBSOLETE</div>	<div>△</div>	5	10.2	4	4	2	6	1-1318115-3
	-	5	10.2	4	4	2	6	1-1318115-3
FINISH		A	B	C	D	N	POS	P/N

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1318115-6](#)