




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-20-013532	23SEP2020	ED	RS


NOTES:

- 1 SINGLE PACKING: ONE CONNECTOR PER LABELED BAG PACKAGED. LABELED PER TEC-107-115
- 2 TRAY PACKAGED
- 3 Au PLATING
- 4 ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC - 4 GHz
NOMINAL IMPEDANCE: 50 Ohm
INSULATION RESISTANCE: 1000 MOhm
WORKING VOLTAGE: 250 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 750 Volts RMS Max
CONTACT RESISTANCE: 6.00 mOhm Max
CENTRE CONTACT: 1.00 mOhm Max
OUTER CONTACT:
- 5 MECHANICAL CHARACTERISTICS
DURABILITY: 500 Cycles Min
- 6 ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -65°C to +165°C



RECOMMENDED PCB LAYOUT

		1	1	BRASS	⚠	CONTACT	3
		1	1	PTFE		INSULATION	2
		1	1	BRASS	⚠	BODY	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		⚠	⚠				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL CHK S.PARLOW APVD F.WHEELER-KING PRODUCT SPEC — APPLICATION SPEC — WEIGHT 0.000000		13FEB06 13FEB06 13FEB06		TE Connectivity NAME SMB SURFACE MOUNT STRAIGHT PCB SOCKET 50 OHM — SIZE A3 CAGE CODE 00779 DRAWING NO C-1337604 RESTRICTED TO —					
DIMENSIONS: mm		0 PLC ± — 1 PLC ± 0.2 2 PLC ± 0.1 3 PLC ± — 4 PLC ± — ANGLES ± —									
											
MATERIAL SEE TABLE		FINISH —		CUSTOMER DRAWING		SCALE NTS		SHEET 1 OF 1		REV D1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1337604-0](#)