





- NOTES:
- 1 MATERIAL HOUSING : GREY GLASSFILLED POLYESTER  
CONTACT : PHOSPHORBRONZE
  - 2 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN. AND ACTION PIN: 0,5µm TIN-LEAD MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
  - 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
  - 4 CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR.
  - 5 CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE
  - 6 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.
  - 7 AREA FOR KEYING PART (BASIC PART NUMBER 100525).



|                                        |  |                           |
|----------------------------------------|--|---------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN L.v.d.HEIJDEN 18MAY99 |
| DIMENSIONS: MM                         |  | CHK D. TRUREN             |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD F.v.KONINGSBRUGGE    |
| 0 PLC ± -                              |  | PRODUCT SPEC              |
| 1 PLC ± -                              |  | APPLICATION SPEC          |
| 2 PLC ± -                              |  | 114-19029                 |
| 3 PLC ± -                              |  | WEIGHT -                  |
| 4 PLC ± -                              |  | CUSTOMER DRAWING          |
| ANGLES ± -                             |  |                           |
| FINISH -                               |  |                           |

| LOC | DIST | REVISIONS |     |               |          |      |      |
|-----|------|-----------|-----|---------------|----------|------|------|
|     |      | P         | LTR | DESCRIPTION   | DATE     | DWN  | APVD |
| H   | -    |           | C   | EHC0-0195-04  | 07-07-04 | DvdB | BM   |
|     |      |           | D   | EH10-0680-05  | 06-06-05 | BSV  | BM   |
|     |      |           | D1  | ECR-06-002635 | 07-02-06 | BSV  | BM   |

RECOMMENDED PCB-HOLE LAY-OUT  
COMPONENT SIDE SHOWN

CONTACT LAYOUT

|                      | a | b | c | d | e |
|----------------------|---|---|---|---|---|
| 1                    | 1 | 2 | 2 | 2 | 2 |
| 2                    | 2 | 2 | 2 | 2 | 2 |
| 3                    | 2 | 2 | 2 | 2 | 2 |
| 4                    | 2 | 2 | 2 | 2 | 2 |
| 5                    | 2 | 2 | 2 | 2 | 2 |
| 6                    | 2 | 2 | 2 | 2 | 2 |
| 7                    | 2 | 2 | 2 | 2 | 2 |
| 8                    | 2 | 2 | 2 | 2 | 2 |
| 9                    | 2 | 2 | 2 | 2 | 2 |
| 10                   | 2 | 2 | 2 | 2 | 2 |
| 11                   | 2 | 2 | 2 | 2 | 2 |
| MULTI PURPOSE CENTRE |   |   |   |   |   |
| 15                   | 3 | 2 | 3 | 2 | 2 |
| 16                   | 2 | 2 | 2 | 2 | 2 |
| 17                   | 2 | 2 | 2 | 2 | 2 |
| 18                   | 2 | 2 | 2 | 2 | 2 |
| 19                   | 2 | 2 | 2 | 2 | 2 |
| 20                   | 2 | 2 | 2 | 2 | 2 |
| 21                   | 2 | 2 | 2 | 2 | 2 |
| 22                   | 2 | 2 | 2 | 2 | 2 |
| 23                   | 2 | 2 | 2 | 2 | 2 |
| 24                   | 2 | 2 | 2 | 2 | 2 |
| 25                   | 2 | 2 | 2 | 2 | 2 |

P.C.B. HOLE DIM. ACTION PIN  
FOR DETAILS SEE APPLICATION SPECIFICATION

|                |          |             |
|----------------|----------|-------------|
| CONTACT FINISH | MATERIAL | PARTNUMBER  |
| 2/3            | 1        | 1-1345055-1 |
| 2/3            | 1        | 1345055-1   |

|                                        |  |                           |                      |  |                               |  |
|----------------------------------------|--|---------------------------|----------------------|--|-------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN L.v.d.HEIJDEN 18MAY99 | tyco Electronics     |  | Tyco Electronics Corporation  |  |
| DIMENSIONS: MM                         |  | CHK D. TRUREN             | NAME                 |  | s-HertogenBosch, Netherlands, |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD F.v.KONINGSBRUGGE    | Z-PACK 2MM HM TYPE A |  | 110 POS. RIGHT ANGLE MALE     |  |
| 0 PLC ± -                              |  | PRODUCT SPEC              | CONNECTOR ASSEMBLY   |  | RESTRICTED TO                 |  |
| 1 PLC ± -                              |  | APPLICATION SPEC          | 114-19029            |  | -                             |  |
| 2 PLC ± -                              |  | WEIGHT -                  | A2 00779             |  | C=1345055                     |  |
| 3 PLC ± -                              |  | CUSTOMER DRAWING          | SCALE NTS            |  | SHEET 1 OF 1                  |  |
| 4 PLC ± -                              |  |                           |                      |  | REV D1                        |  |
| ANGLES ± -                             |  |                           |                      |  |                               |  |
| FINISH -                               |  |                           |                      |  |                               |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1345055-1](#)