




- 1 STAMP AMP 16-14* APPROX AS SHOWN
- 2 MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS
- 3 MATERIAL:
COPPER PER ASTM B152
- 4 FINISH:
GOLD 0.001270[.000050] MIN THK PER
ASTM B488 TYPE 1, CODE C
OVER NICKEL PLATE 0.000762[.000030] MIN
THK PER SAE AMS QQ-N-290

500	LOOSE PIECE	134540-1
QTY	PACKAGE TYPE	PART NUMBER

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	25JUN2018
-----	-----------

RAVI S	
CHK	25JUN2018

CHK	25JUN2018
ROHDE DANIEL F	

APVD	25JUN2018
------	-----------

ROHDE DANIEL F
PRODUCT SPEC

—

APPLICATION SPEC

	—
WEIGHT	



TE Connectivity Ltd.

3	NAME
---	------

BUTT SPLICE SOLISTRAND
16-14 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

SIZE	SIZE CODE	DRAWING NO.	RESTRICTED TO
A3	00779	C-134540	—

CUSTOMER DRAWING	SCALE	8:1	SHEET	1	OF	1	REV	A
------------------	-------	-----	-------	---	----	---	-----	---

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

MAX RECOMMENDED OPERATING TEMPERATURE:	260°C [500°F]
--	---------------

VOLTAGE RATING:

N/A

FOR APPLICATION

TOOLING ASSISTANCE CENTER


TOOLING INFORMATION

1-800-722-1111

1-800-526-5142

WIRE CROSS SECTIONAL AREA RANGE,
1.04-2.62mm²[2,050-5,180] CIR MILS

DIMENSIONS:
mm [INCHES]



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0	PLC	$\pm -$
1	PLC	$\pm -$
2	PLC	$\pm -$
3	PLC	$\pm 0.127[.005]$
4	PLC	$\pm -$
ANGLES		$\pm 5^\circ$

ANGLES
FINISH

3

4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[134540-1](#)