

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AJ	-	C		RDW & REV PER 0S14-0295-05	20JUL04	KW

D



C

B

A



.036 / 0.8 SQ.  
4 PLACES



D

C

B

A

1363128

1363128-1  
PART NUMBER

HOUSING CAP	BRASS PER QQ-B-626 COMP. 360	GOLD PLATE PER MIL-G-45204
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
COMPONENT	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RMF 03DEC99	<b>tyco</b> Electronics		Tyco Electronics Corporation Middletown, PA 17057	
DIMENSIONS: INCHES		CHK -			NAME MCX R/A PCB JACK, 75 OHM	
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD RMF 15DEC99	SIZE		CAGE CODE	DRAWING NO
		PRODUCT SPEC	A2		00779	C=1363128
		APPLICATION SPEC	WEIGHT		-	RESTRICTED TO -
MATERIAL -	FINISH -	CUSTOMER DRAWING	SCALE 11:1		SHEET 1 OF 1	REV C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1363128-1](#)