

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

D7

OBSOLETING PART NUMBERS 15 POSITION AND ABOVE

09APR2015

CR

PS

MATERIAL:

HOUSING: NYLON, UL94V-0, BLACK.

TERMINAL: BRIGHT TIN PLATED, COPPER ALLOY.

SCREW: 6-32, STEEL, ZINC PLATED CLEAR

CHROMATE, UNLESS OTHERWISE STATED.

ELECTRICAL:

UL CLASS C: 20A, 150V.

UL CLASS D: 10A, 300V.

CSA TYPE B: 20A, 300V.

CSA TYPE C: 20A, 300V.

CSA TYPE D: 10A, 300V.

CSA TYPE E 20A, 300V.

WIRE RANGE: 12-22 AWG

MECHANICAL:

MAXIMUM TORQUE RATING: 7 IN-LB.

RECOMMENDED PCB LAYOUT

1 MIDDLE TERMINAL IS ROTATED 180° FROM OTHERS. NOT TO BE USED WITH RECOMMENDED PCB LAYOUT.

2 OBSOLETE PART NUMBER.





3 PRELIMINARY PART NUMBER.

4 SCREWS ARE NICKEL PLATED BRASS.

5 SEE FIGURE.

6 SPECIAL FULL THREAD BINDER HD SCREW USED FOR THIS ASSY ONLY ALLOWS FOR USE OF J4 JUMPER.

7 OBSOLETE PARTS.



7	OBSOLETE	.160	7.540	-	-	-	23	4DB-P107-23	2-1546468-3
7	OBSOLETE	.160	7.215	-	-	-	22	4DB-P107-22	2-1546468-2
7	OBSOLETE	.160	6.890	-	-	-	21	4DB-P107-21	2-1546468-1
7	OBSOLETE	.160	6.565	-	-	-	20	4DB-P107-20	2-1546468-0
7	OBSOLETE	.160	6.240	-	-	-	19	4DB-P107-19	1-1546468-9
7	OBSOLETE	.160	5.915	-	-	-	18	4DB-P107-18	1-1546468-8
7	OBSOLETE	.160	5.590	-	-	-	17	4DB-P107-17	1-1546468-7
7	OBSOLETE	.160	5.265	-	-	-	16	4DB-P107-16	2-1437667-1
7	OBSOLETE	.160	4.940	-	-	-	15	4DB-P107-15	2-1437667-0
4	3	.160	4.615	-	-	-	14	4DB-P105-14	4-1546468-0
		.160	4.615	-	-	-	14	4DB-P107-14	1-1546468-4
		.160	4.290	-	-	-	13	4DB-P107-13	1-1546468-3
4	3	.160	3.965	-	-	-	12	4DB-P105-12	3-1546468-9
		.160	3.965	-	-	-	12	4DB-P107-12	1-1437667-9
		.160	3.640	-	-	-	11	4DB-P107-11	1-1437667-8
5	4	3	.160	3.315	-	10	10	4DB-P105-10-104	4-1546468-2
			.160	3.315	-	-	10	4DB-P107-10	1-1437667-7
			.160	2.990	-	-	9	4DB-P105-09	3-1546468-8
			.160	2.990	-	-	9	4DB-P107-09	1-1437667-6
4	3	.160	2.665	-	-	-	8	4DB-P105-08	3-1546468-7
		.160	2.665	-	-	-	8	4DB-P107-08	1-1437667-5
4	3	.160	2.340	-	-	-	7	4DB-P105-07	3-1546468-6
		.160	2.340	-	-	-	7	4DB-P107-07	1-1437667-4
4	3	.160	2.015	-	-	-	6	4DB-P105-06	3-1546468-5
		.160	2.015	-	-	-	6	4DB-P107-06	1-1437667-2
4	3	.160	1.690	-	-	-	5	4DB-P105-05	3-1546468-4
		.160	1.690	-	-	-	5	4DB-P107-05	1-1437667-1
	6	.160	1.365	-	-	-	4	4DB-P107-04	4-1546468-5
4	3	.160	1.365	-	-	-	4	4DB-P105-04	3-1546468-3
		.160	1.365	-	-	-	4	4DB-P107-04	1-1437667-0
	6	.122±.012	1.040	-	-	-	3	4DB-P107-03	4-1546468-4
SEE FIGURE 1	2	.160	1.040	-	-	-	3	4DB-P107-03-070	1437667-9
SEE FIGURE 3		.160	1.040	-	-	-	3	4DB-P107-03-096	3-1546468-2
7	OBSOLETE	.160	1.040	-	-	-	3	4DB-P107-03-095	3-1546468-1
		.160	1.040	-	-	-	3	4DB-P107-03	1437667-7
4	3	.160	.715	-	-	-	2	4DB-P105-02	4-1546468-3
		.160	.715	-	-	-	2	4DB-P107-02	1437667-6
		DIM B	DIM A	.187 QC TAB 90° DOUBLE SIDED 3	.187 QC TAB 45° DOUBLE SIDED 2	.187 QC TAB FLAT DOUBLE SIDED 1	NO. OF POS.	CATATLOG NUMBER	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S SCHLEGEL 10/19/04

CHK S YODER 10/19/04

APVD S YODER 10/19/04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

STE

TE Connectivity

NAME

4DB SERIES

P107 STYLE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=

1437667-6

SCALE

NTS

SHEET

1 OF 2

REV

D7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1437667-4](#)