


1. APPLIED CONTACT PART NUMBERS:
175265 TIN PLATING, 040 CONTACT
175266 SELECT GOLD PLATING, 040 CONTACT
1326030 TIN PLATING, 2.8 CONTACT
2. LOCK PLATE SHOWN IN THE SHIPPING POSITION.
3. VISUAL BLEMISHES MAY BE PRESENT ON EXTERNAL SURFACES DUE TO BULK PACKAGING METHODS. THESE BLEMISHES THAT DO NOT AFFECT CONNECTOR FORM, FIT, OR FUNCTION ARE CONSIDERED ACCEPTABLE.
4. LOCK PLATE COMPONENT FORCES:
INSERTION FORCE (SEATING): 75N MAX.
REMOVAL FROM PLUG HOUSING: 15N MIN.



- KEY "B" SHOWN -		
GRAY	A	I438761-6
BLACK	C	I438759-2
WHITE	B	I438759-1
COLOR	KEY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. HITCHCOCK 16SEP2004 CHK G. MARTIN 16SEP2004 APVD E. McHAFFEE 16SEP2004		COLOR RET PART NUMBER	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.3 2 PLC ±0.1 3 PLC ±. 4 PLC ±. ANGLES ±1°		 TE Connectivity PLUG ASSEMBLY, 22-WAY HYBRID 040/2.8	
MATERIAL PBT FINISH - WEIGHT -		NAME 108-2217 APPLICATION SPEC 114-13158 Customer Drawing		SIZE CAGE CODE DRAWING NO A100779 C-1438759 SCALE A:1 SHEET 1 OF 1 REV F	
				RESTRICTED TO	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1438759-1](#)