






5 PLATING: CONTACTS - 0.76μm MINIMUM GOLD ON MATING END,
2.54μm MINIMUM MATTE TIN ON SOLDER TAILS, BOTH OVER
1.27μm MINIMUM NICKEL.
HOLD DOWNS: 2.54μm MINIMUM MATTE TIN OVER 1.27μm MINIMUM
NICKEL.



	REVERSE TAPED		9.00	16.41	16.00	4	6-1445100-4
	TAPED		33.00	40.41	40.00	12	3-1445100-2
	TAPED		30.00	37.41	37.00	11	3-1445100-1
	TAPED		27.00	34.41	34.00	10	3-1445100-0
	TAPED		24.00	31.41	31.00	9	2-1445100-9
	TAPED		21.00	28.41	28.00	8	2-1445100-8
	TAPED		18.00	25.41	25.00	7	2-1445100-7
	TAPED		15.00	22.41	22.00	6	2-1445100-6
	TAPED		12.00	19.41	19.00	5	2-1445100-5
	TAPED		9.00	16.41	16.00	4	2-1445100-4
	TAPED		6.00	13.41	13.00	3	2-1445100-3
	TAPED		3.00	10.41	10.00	2	2-1445100-2
2	TAPED		33.00	40.41	40.00	12	1-1445100-2
1	TAPED		30.00	37.41	37.00	11	1-1445100-1
0	TAPED		27.00	34.41	34.00	10	1-1445100-0
9	TAPED		24.00	31.27	31.00	9	1445100-9
8	TAPED		21.00	28.41	28.00	8	1445100-8
7	TAPED		18.00	25.41	25.00	7	1445100-7
6	TAPED		15.00	22.41	22.00	6	1445100-6
5	TAPED		12.00	19.41	19.00	5	1445100-5
4	TAPED		9.00	16.41	16.00	4	1445100-4
3	TAPED		6.00	13.41	13.00	3	1445100-3
2	TAPED		3.00	10.41	10.00	2	1445100-2
	PACKAGING	FINISH	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN J ROOT 09OCT2000		TE Connectivity					
DIMENSIONS: mm 						CHK K WHITAKER 17-APR-2001		NAME RIGHT ANGLE SURFACE MNT HEADER ASSY, 0.76 MIC GOLD CONTACTS,W/SURF MOUNT HOLDDOWNS,SGL ROW,MICRO MATE-N-LOK™					
						APVD C JONES 17-APR-2001							
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH SEE TABLE						PRODUCT SPEC 108-1836				SIZE A2	CAGE CODE 00779	DRAWING NO C-1445100	RESTRICTED TO -
						APPLICATION SPEC 114-13000							
MATERIAL 						WEIGHT -		SCALE 5:1		SHEET 1 OF 1	REV C4		
CUSTOMER DRAWING													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-1445100-4](#)