


D

B



- 1

THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 2

0.000762[.000030] GOLD ON CONTACT AREA, 0.00254[.000100]–0.00508[.000200] MATTE TIN–LEAD ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.
- 3



HOUSING: LCP, COLOR–BLACK. POSTS: COPPER ALLOY.
- 4

0.000762[.000030] GOLD ON CONTACT AREA, 0.00254[.000100]–0.00508[.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.
- 5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI


C

C



B

B



5

OBSOLETE

5

OBSOLETE

4	35.56 [1.400]	14	35.69 [1.484]	15	6–146128–3
4	33.02 [1.300]	13	33.15 [1.384]	14	6–146128–2
4	30.48 [1.200]	12	30.61 [1.284]	13	6–146128–1
4	27.94 [1.100]	11	28.07 [1.184]	12	6–146128–0
4	25.40 [1.000]	10	27.53 [1.084]	11	5–146128–9
4	22.86 [.900]	9	24.99 [.984]	10	5–146128–8
4	20.32 [.800]	8	22.45 [.884]	9	5–146128–7
4	17.78 [.700]	7	19.91 [.784]	8	5–146128–6
4	15.24 [.600]	6	17.37 [.684]	7	5–146128–5
4	12.70 [.500]	5	14.83 [.584]	6	5–146128–4
4	10.16 [.400]	4	12.29 [.484]	5	5–146128–3
4	7.62 [.300]	3	9.75 [.384]	4	5–146128–2
4	5.08 [.200]	2	7.21 [.284]	3	5–146128–1
2	35.56 [1.400]	14	35.69 [1.484]	15	1–146128–3
2	33.02 [1.300]	13	33.15 [1.384]	14	1–146128–2
2	30.48 [1.200]	12	30.61 [1.284]	13	—1–146128–1—
2	27.94 [1.100]	11	28.07 [1.184]	12	—1–146128–0—
2	25.40 [1.000]	10	27.53 [1.084]	11	—146128–9—
2	22.86 [.900]	9	24.99 [.984]	10	—146128–8—
2	20.32 [.800]	8	22.45 [.884]	9	146128–7
2	17.78 [.700]	7	19.91 [.784]	8	146128–6
2	15.24 [.600]	6	17.37 [.684]	7	—146128–5—
2	12.70 [.500]	5	14.83 [.584]	6	146128–4
2	10.16 [.400]	4	12.29 [.484]	5	146128–3
2	7.62 [.300]	3	9.75 [.384]	4	146128–2
2	5.08 [.200]	2	7.21 [.284]	3	146128–1
PLATING	C	B	A	NO OF POSN	PART NUMBER

A

A

RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL

THIS DRAWING IS A CONTROLLED DOCUMENT.

30–09–94

J KNAUB

30–09–94

G DUBNICZKI

CHK

30–09–94

G DUBNICZKI

APVD

NAME

TE Connectivity

PRODUCT SPEC

NAME

APPLICATION SPEC

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

—

A1

00779

146128

CUSTOMER DRAWING

SCALE

10:1

SHEET

1

OF

1

REV

L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-146128-2](#)