







	35.56 [1.400]	14	37.69 [1.484]	30	6-146130-4
	33.02 [1.300]	13	35.15 [1.384]	28	6-146130-3
	30.48 [1.200]	12	32.61 [1.284]	26	6-146130-2
	27.94 [1.100]	11	30.07 [1.184]	24	6-146130-1
	25.40 [1.000]	10	27.53 [1.084]	22	6-146130-0
	22.86 [.900]	9	24.99 [.984]	20	5-146130-9
	20.32 [.800]	8	22.45 [.884]	18	5-146130-8
	17.78 [.700]	7	19.91 [.784]	16	5-146130-7
	15.24 [.600]	6	17.37 [.684]	14	5-146130-6
	12.70 [.500]	5	14.83 [.584]	12	5-146130-5
	10.16 [.400]	4	12.29 [.484]	10	5-146130-4
	7.62 [.300]	3	9.75 [.384]	8	5-146130-3
	5.08 [.200]	2	7.21 [.284]	6	5-146130-2
	2.54 [.100]	1	4.67 [.184]	4	5-146130-1
E 	17.78 [.700]	7	19.91 [.784]	16	1-146130-8
E 	5.08 [.200]	2	7.21 [.284]	6	1-146130-7
	35.56 [1.400]	14	37.69 [1.484]	30	1-146130-4
E 	33.02 [1.300]	13	35.15 [1.384]	28	1-146130-3
	30.48 [1.200]	12	32.61 [1.284]	26	1-146130-2
	27.94 [1.100]	11	30.07 [1.184]	24	1-146130-1
D 	25.40 [1.000]	10	27.53 [1.084]	22	1-146130-0
	22.86 [.900]	9	24.99 [.984]	20	146130-9
	20.32 [.800]	8	22.45 [.884]	18	146130-8
	17.78 [.700]	7	19.91 [.784]	16	146130-7
	15.24 [.600]	6	17.37 [.684]	14	146130-6
	12.70 [.500]	5	14.83 [.584]	12	146130-5
	10.16 [.400]	4	12.29 [.484]	10	146130-4
	7.62 [.300]	3	9.75 [.384]	8	146130-3
	5.08 [.200]	2	7.21 [.284]	6	146130-2
	2.54 [.100]	1	4.67 [.184]	4	146130-1
PLATING	C	B	A	NO OF POSN	PART NUMBER

EF  OBSOLETE

6 OBSOLETE

7 OBSOLETE

~~7~~ SUPERSEDED BY 6-146130-0



RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J. KNAUB 30-09-94		 TE Connectivity	
DIMENSIONS: mm [INCHES]		QIR G DUBNICZKI 30-09-94 APVD G DUBNICZKI 30-09-94			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		SURFACE MOUNT HEADER ASSEMBLY, MOD. II, BREAKAWAY, VERTICAL, DOUBLE ROW, 100 X 100 CL, .025 SQ. POST	
 0 P.LC ± — 2 P.LC ± — 3 P.LC ± 0.13[.005] 4 P.LC ± — ANGLES ± 1°		APPLICATION SPEC			
MATERIAL		FINISH		WEIGHT — A1 00779 ©=146130	
 SEE TABLE		CUSTOMER DRAWING			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-146130-0](#)