















RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL



	35.56 [1.400]	14	37.69 [1.484]	30	6-146131-4
	33.02 [1.300]	13	35.15 [1.384]	28	6-146131-3
	30.48 [1.200]	12	32.61 [1.284]	26	6-146131-2
	27.94 [1.100]	11	30.07 [1.184]	24	6-146131-1
	25.40 [1.000]	10	27.53 [1.084]	22	6-146131-0
	22.86 [.900]	9	24.99 [.984]	20	5-146131-9
	20.32 [.800]	8	22.45 [.884]	18	5-146131-8
	17.78 [.700]	7	19.91 [.784]	16	5-146131-7
	15.24 [.600]	6	17.37 [.684]	14	5-146131-6
	12.70 [.500]	5	14.83 [.584]	12	5-146131-5
	10.16 [.400]	4	12.29 [.484]	10	5-146131-4
	7.62 [.300]	3	9.75 [.384]	8	5-146131-3
	5.08 [.200]	2	7.21 [.284]	6	5-146131-2
	2.54 [.100]	1	4.67 [.184]	4	5-146131-1
	35.56 [1.400]	14	37.69 [1.484]	30	1-146131-4
	33.02 [1.300]	13	35.15 [1.384]	28	1-146131-3
	30.48 [1.200]	12	32.61 [1.284]	26	1-146131-2
	27.94 [1.100]	11	30.07 [1.184]	24	1-146131-1
	25.40 [1.000]	10	27.53 [1.084]	22	1-146131-0
	22.86 [.900]	9	24.99 [.984]	20	146131-9
	20.32 [.800]	8	22.45 [.884]	18	146131-8
	17.78 [.700]	7	19.91 [.784]	16	146131-7
	15.24 [.600]	6	17.37 [.684]	14	146131-6
	12.70 [.500]	5	14.83 [.584]	12	146131-5
	10.16 [.400]	4	12.29 [.484]	10	146131-4
	7.62 [.300]	3	9.75 [.384]	8	146131-3
	5.08 [.200]	2	7.21 [.284]	6	146131-2
	2.54 [.100]	1	4.67 [.184]	4	146131-1
PLATING	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. J. KNAUB 30-09-94		 TE Connectivity	
		CHK. G. DUBNICZKI 30-09-94			
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
mm [INCHES]		APVD. G. DUBNICZKI 30-09-94		SURFACE MOUNT HEADER ASSEMBLY,	
		PRODUCT SPEC		MOD II, BREAKAWAY, VERTICAL,	
		APPLICATION SPEC		DOUBLE ROW, .100 X.100 C/L, .025 SQ.POST	
		SIZE		CASE CODE	
		DRAWING NO		RESTRICTED TO	
		WEIGHT		—	
MATERIAL		FINISH		A1 00779	
SEE TABLE		CUSTOMER DRAWING		SCALE 8:1 SHEET 1 of 1 REV H	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-146131-2](#)