




RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL

- | 5 | 33.02
[.300] | 13 | 35.15
[.384] | 28 | 6-146134-3 |
|---------|-----------------|----|-----------------|---------------|-----------------------|
| 5 | 30.48
[.200] | 12 | 32.61
[.284] | 26 | 6-146134-2 |
| 5 | 27.94
[.100] | 11 | 30.07
[.184] | 24 | 6-146134-1 |
| 5 | 25.40
[.000] | 10 | 27.53
[.084] | 22 | 6-146134-0 |
| 5 | 22.86
[.900] | 9 | 24.99
[.984] | 20 | 5-146134-9 |
| 5 | 20.32
[.800] | 8 | 22.45
[.884] | 18 | 5-146134-8 |
| 5 | 15.24
[.600] | 6 | 17.37
[.684] | 14 | 5-146134-6 |
| 5 | 12.70
[.500] | 5 | 14.83
[.584] | 12 | 5-146134-5 |
| 5 | 7.62
[.300] | 3 | 9.75
[.384] | 8 | 5-146134-3 |
| 5 | 5.08
[.200] | 2 | 7.21
[.284] | 6 | 5-146134-2 |
| 5 | 2.54
[.100] | 1 | 4.67
[.184] | 4 | 5-146134-1 |
| 5 | 35.56
[.400] | 14 | 37.69
[.484] | 30 | 2-146134-1 |
| 5 | 17.78
[.700] | 7 | 19.91
[.784] | 16 | 1-146134-9 |
| 5 | 15.24
[.600] | 6 | 17.37
[.684] | 14 | 1-146134-8 |
| 5 | 10.16
[.400] | 4 | 12.29
[.484] | 10 | 1-146134-7 |
| 5 | 5.08
[.200] | 2 | 7.21
[.284] | 6 | 1-146134-6 |
| 3 | 35.56
[.400] | 14 | 37.69
[.484] | 30 | 1-146134-4 |
| 3 | 33.02
[.300] | 13 | 35.15
[.384] | 28 | 1-146134-3 |
| 3 | 30.48
[.200] | 12 | 32.61
[.284] | 26 | 1-146134-2 |
| 3 | 27.94
[.100] | 11 | 30.07
[.184] | 24 | 1-146134-1 |
| 3 | 25.40
[.000] | 10 | 27.53
[.084] | 22 | 1-146134-0 |
| 3 | 22.86
[.900] | 9 | 24.99
[.984] | 20 | 146134-9 |
| 3 | 20.32
[.800] | 8 | 22.45
[.884] | 18 | 146134-8 |
| 3 | 17.78
[.700] | 7 | 19.91
[.784] | 16 | 146134-7 |
| 3 | 15.24
[.600] | 6 | 17.37
[.684] | 14 | 146134-6 |
| 3 | 12.70
[.500] | 5 | 14.83
[.584] | 12 | 146134-5 |
| 3 | 10.16
[.400] | 4 | 12.29
[.484] | 10 | 146134-4 |
| 3 | 7.62
[.300] | 3 | 9.75
[.384] | 8 | 146134-3 |
| 3 | 5.08
[.200] | 2 | 7.21
[.284] | 6 | 146134-2 |
| 3 | 2.54
[.100] | 1 | 4.67
[.184] | 4 | 146134-1 |
| PLATING | C | B | A | NO OF
POSN | PART
NUMBER |

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-146134-8](#)