


- |   |                                                                                                                                                     |
|---|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| 1 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.                                                                             |
| 2 | BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT ( AS SHOWN ) OR TO THE LEFT                                                                      |
| 3 | 0.000762 [.000030] GOLD ON CONTACT AREA,<br>0.00254-0.00508 [.000100-.000200] MATTE,<br>TIN-LEAD ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL. |
| 4 | HOUSING: GLASS FILLED THERMOPLASTIC, COLOR, BLACK.<br>( WILL WITHSTAND VAPOR PHASE REFLOW.)<br>CONTACT: COPPER ALLOY.                               |
| 5 | 0.000762 [.000030] GOLD ON CONTACT AREA,<br>0.00254-0.00508 [.000100-.000200] MATTE TIN,<br>ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.      |
| 6 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI                                                                                     |





# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-146304-6](#)