





- | | | | | | |
|-----------------------|---------------------------|--------------|--------------|----|------------------------|
| SUPERSEDED 6-146762-2 | $\triangle_2$ | 15.24[.600] | 17.78[.700] | 14 | 1-146762-2 |
| | $\triangle_2$ | 12.70[.500] | 15.24[.600] | 12 | 1-146762-1 |
| SUPERSEDED 6-146762-0 | $\triangle_9 \triangle_2$ | -5.08[.200] | 7.62[.300] | 6 | 1-146762-0 |
| SUPERSEDED 5-146762-9 | $\triangle_9 \triangle_2$ | -2.54[.100] | 5.08[.200] | 4 | 146762-9 |
| | $\triangle_9 \triangle_2$ | - | 2.54[.100] | 2 | $\triangle_6$ 146762-8 |
| | $\triangle_2$ | 22.86[.900] | 25.40[1.000] | 20 | 146762-7 |
| | $\triangle_2$ | 78.74[3.100] | 81.28[3.200] | 64 | 146762-6 |
| | $\triangle_2$ | 48.26[1.900] | 50.80[2.000] | 40 | 146762-5 |
| | $\triangle_2$ | 35.56[1.400] | 38.10[1.500] | 30 | 146762-4 |
| | $\triangle_2$ | 20.32[.800] | 22.86[.900] | 18 | 146762-3 |
| | $\triangle_9 \triangle_2$ | 10.16[.400] | 12.70[.500] | 10 | 146762-2 |
| | $\triangle_9 \triangle_2$ | 7.62[.300] | 10.16[.400] | 8 | 146762-1 |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER		06NOV2002		 TE Connectivity	
		CHK J.JOLSON		06NOV02			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.JOLSON		NAME	
		0 PLC ± -		PRODUCT SPEC 108-25022		RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, TOP ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		1 PLC ± -					
		2 PLC ± 0.13[.005]		APPLICATION SPEC		SIZE	
		3 PLC ± -		114-25018		CAGE CODE	
		4 PLC ± -		WEIGHT		DRAWING NO	
MATERIAL		FINISH		A2		00779	
		 		C-146762		RESTRICTED TO	
				CUSTOMER DRAWING		SCALE 4:1	
						SHEET 1 of 2	
						REV .15	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By - ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	OWN	APVD
			—	SEE SHEET I	—	—	—

	99.06[3.900]	101.60[4.000]	80		9-146762-0
	96.52[3.800]	99.06[3.900]	78		8-146762-9
	93.98[3.700]	96.52[3.800]	76		8-146762-8
	91.44[3.600]	93.98[3.700]	74		8-146762-7
	88.90[3.500]	91.44[3.600]	72		8-146762-6
	86.36[3.400]	88.90[3.500]	70		8-146762-5
	83.82[3.300]	86.36[3.400]	68		8-146762-4
	81.28[3.200]	83.82[3.300]	66		8-146762-3
	76.20[3.000]	78.74[3.100]	62		8-146762-2
	73.66[2.900]	76.20[3.000]	60		8-146762-1
	71.12[2.800]	73.66[2.900]	58		8-146762-0
	68.58[2.700]	71.12[2.800]	56		7-146762-9
	66.04[2.600]	68.58[2.700]	54		7-146762-8
	63.50[2.500]	66.04[2.600]	52		7-146762-7
	60.96[2.400]	63.50[2.500]	50		7-146762-6
	58.42[2.300]	60.96[2.400]	48		7-146762-5
	55.88[2.200]	58.42[2.300]	46		7-146762-4
	53.34[2.100]	55.88[2.200]	44		7-146762-3
	50.80[2.000]	53.34[2.100]	42		7-146762-2
	45.72[1.800]	48.26[1.900]	38		7-146762-1
	43.18[1.700]	45.72[1.800]	36		7-146762-0
	40.64[1.600]	43.18[1.700]	34		6-146762-9
	38.10[1.500]	40.64[1.600]	32		6-146762-8
	33.02[1.300]	35.56[1.400]	28		6-146762-7
	30.48[1.200]	33.02[1.300]	26		6-146762-6
	27.94[1.100]	30.48[1.200]	24		6-146762-5
	25.40[1.000]	27.94[1.100]	22		6-146762-4
	17.78[.700]	20.32[.800]	16		6-146762-3
	15.24[.600]	17.78[.700]	14		6-146762-2
	12.70[.500]	15.24[.600]	12		6-146762-1
	5.08[.200]	7.62[.300]	6		6-146762-0
	2.54[.100]	5.08[.200]	4		5-146762-9
		2.54[.100]	2		5-146762-8
	22.86[.900]	25.40[1.000]	20		5-146762-7
	78.74[3.100]	81.28[3.200]	64		5-146762-6
	48.26[1.900]	50.80[2.000]	40		5-146762-5
	35.56[1.400]	38.10[1.500]	30		5-146762-4
	20.32[.800]	22.86[.900]	18		5-146762-3
	10.16[.400]	12.70[.500]	10		5-146762-2
	7.62[.300]	10.16[.400]	8		5-146762-1
FINISH	B	A	NO OF POSN		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER		06NOV2002		 TE Connectivity	
		CHK J. OLSON		06NOV02			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. OLSON		NAME	
		0 PLC ± -		PRODUCT SPEC		RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, TOP ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		1 PLC ± -		108-25022			
		2 PLC ± 0.13[.005]		APPLICATION SPEC			
		3 PLC ± -		114-25018		SIZE	
		4 PLC ± -		WEIGHT		CAGE CODE	
MATERIAL		FINISH		A2		DRAWING NO	
		 		00779		RESTRICTED TO	
				C-146762		—	
CUSTOMER DRAWING						SCALE 1:1	
						SHEET 2 of 2	
						REV J5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146762-1](#)