

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC
JDIST
-

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

C1 REVISED PER ECO-11-005030

26APR11 RK HMR

1473562-4:AS SHOWN
1473562-4:本図

1. 材料: PLUG HOUSING: ガラス入り熱可塑性ポリエステル樹脂 94V-0 黒
HOLD HOUSING: ポリカーボネイト 94V-0 黄色: 0-、赤色: 1-、青色: 2-
コンタクト: 銅合金



2. メッキ: 全面Ni下地: 1.27μm以上
接点部: 0.2μm MIN 金メッキ



3. -5(5POS)と-7(7POS)は、回路番号6と8にコンタクトが装着されません

NOTE



1. MATERIAL: PLUG HOUSING: GLASS FILED THERMOPLASTIC, 94V-0, BLACK
HOLD HOUSING: PC, 94V-0, YELLOW: 0-, RED: 1-, BLUE: 2-
CONTACT: COPPER ALLOY



2. FINISH: UNDERPLATE: Ni 1.27μm min
CONTACT AREA: Au 0.2μm min



3. X--5(5POS) AND X--7(7POS) DO NOT EQUIP WITH CONTACT OF CIRCUIT NO 6 AND 8.

BLUE	20.35	17.2	14	24.1	7	8	2-1473562-8
RED	20.35	17.2	14	24.1	7	8	1-1473562-8
YELLOW	20.35	17.2	14	24.1	7	8	1473562-8
BLUE	20.35	17.2	14	24.1	7	7	3 2-1473562-7
RED	20.35	17.2	14	24.1	7	7	3 1-1473562-7
YELLOW	20.35	17.2	14	24.1	7	7	3 1473562-7
BLUE	16.35	13.2	10	20.1	5	6	2-1473562-6
RED	16.35	13.2	10	20.1	5	6	1-1473562-6
YELLOW	16.35	13.2	10	20.1	5	6	1473562-6
BLUE	16.35	13.2	10	20.1	5	5	3 2-1473562-5
RED	16.35	13.2	10	20.1	5	5	3 1-1473562-5
YELLOW	16.35	13.2	10	20.1	5	5	3 1473562-5
BLUE	12.35	9.2	6	16.1	3	4	2-1473562-4
RED	12.35	9.2	6	16.1	3	4	1-1473562-4
YELLOW	12.35	9.2	6	16.1	3	4	1473562-4
BLUE	10.35	7.2	4	14.1	2	3	2-1473562-3
RED	10.35	7.2	4	14.1	2	3	1-1473562-3
YELLOW	10.35	7.2	4	14.1	2	3	1473562-3
HOLD HSG COLOR	D	C	B	A	N	POS	PART NUMBER

〈Table of Insulation Dia (Cable suitable for e-CON.)〉
〈被覆外径一覧表(e-CON 適応電線)〉

ORANGE	φ0.60~0.90	3-1473562-□	SEE SHEET 3
RED	φ0.90~1.00	1-1473562-□	SEE SHEET 1
YELLOW	φ1.00~1.15	1473562-□	SEE SHEET 1
BLUE	φ1.15~1.35	2-1473562-□	SEE SHEET 1
GREEN	φ1.35~1.60	4-1473562-□	SEE SHEET 2
HOLD HSG COLOR	INSULATION DIA	PART NUMBER	SHEET No

取扱説明書 (Instruction Sheet): 411-78014

DIMENSIONS: 単位: 概 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±3° 3 PLC ± 4 PLC ± ANGLES ±		DWN D. MITSUGI CHK S. MANABE APVD S. MANABE PRODUCT SPEC 108-5765 APPLICATION SPEC 取付適用規格	WIRE RANGE 適合電線断面積 SEE 108-5765		INSULATION DIA 被覆外径		
MATERIAL 材料 SEE NOTE 1		FINISH 仕上 SEE NOTE 2		WEIGHT -		TE Connectivity		NAME 名称 PLUG ASSY FOR e-CON - RITS CONN. -	
CUSTOMER DRAWING		SCALE 尺度 4:1		SHEET 1 OF 3		REV C1		RESTRICTED TO -	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1


-

-

-

4-1473562-4:AS SHOWN

4-1473562-4:本図



① 材料 PLUG HOUSING: ガラス入り熱可塑性ポリエステル樹脂 94V-0 黒
HOLD HOUSING: ポリカーボネイト 94V-0 緑色: 4-
コンタクト: 銅合金






② 仕上げ 全面: ニッケルメッキ下地 1.27μm以上
接点部: 金メッキ 0.2μm以上

③ -5(5POS)と-7(7POS)は、回路番号6と8にコンタクトが装着されません

① MATERIAL PLUG HOUSING: GLASS FIBER THERMOPLASTIC, 94V-0, BLACK
HOLD HOUSING: PC, 94V-0, GREEN: 4-
CONTACT: COPPER ALLOY


② FINISH UNDERPLATE: Ni PLATING ALL SURFACE 1.27μm MIN
CONTACT AREA: Au PLATING 0.2μm MIN

③ -5(5POS) AND -7(7POS) DO NOT EQUIP WITH CONTACT OF CIRCUIT NO 6 AND 8.



取扱説明書 (Instruction Sheet): 411-78014

GREEN	20.35	17.2	14	24.1	7	8	4-1473562-8
	20.35	17.2	14	24.1	7	7	③4-1473562-7
	16.35	13.2	10	20.1	5	6	4-1473562-6
	16.35	13.2	10	20.1	5	5	③4-1473562-5
	12.35	9.2	6	16.1	3	4	4-1473562-4
	10.35	7.2	4	14.1	2	3	4-1473562-3
HOLD HSG COLOR	D	C	B	A	N	POS.	PART NUMBER





		DWN K. RIKU 26DEC02		 TE Connectivity					
		CHK D. MITSUGI 26DEC02							
DIMENSIONS: 単位: 概 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 名称 PLUG ASSY FOR e-CON - RITS CONN. -					
		一般公差 0 PLC ±- ±0.2 1 PLC ±- ±0.3 2 PLC ±- ±0.3 3 PLC ±- ±0.3 4 PLC ±- ±0.3 ANGLES ±-							
MATERIAL 材料 ① SEE NOTE		FINISH 仕上 ② SEE NOTE		APPLICATION SPEC 取付適用規格 -		SIZE 番号 A3	CAGE CODE 00779	DRAWING NO C=1473562	RESTRICTED TO -
CUSTOMER DRAWING						SCALE 尺度 3:1	SHEET 2	OF 3	REV C1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J	-			SEE SHEET 1		

3-1473562-4 : AS SHOWN
3-1473562-4 : 本図


- ① 材料: PLUG HOUSING : ガラス入り熱可塑性ポリエステル樹脂 94V-0 黒
HOLD HOUSING : ポリカーボネイト 94V-0 オレンジ色: 3-
コンタクト: 銅合金
- ② メッキ: 全面ニッケル下地: 1.27μm以上
接点部: 金メッキ: 0.2μm以上
- ③ -5(5POS)と-7(7POS)は、回路番号6と8にコンタクトが装着されません。

- ① MATERIAL: PLUG HOUSING : GLASS FILLED THERMOPLASTIC, 94V-0, BLACK
HOLD HOUSING : PC, 94V-0, ORANGE: 3-
CONTACT : COPPER ALLOY
- ② FINISH: UNDERPLATE : Ni 1.27μm MIN
CONTACT AREA : Au 0.2μm MIN
- ③ -5(5POS) AND -7(7POS) DO NOT EQUIP WITH CONTACT OF CIRCUIT No. 6 & 8.



・取扱説明書 (Instruction Sheet): 411-78010

ORANGE	20.35	17.2	14	24.1	7	8	3-1473562-8
	20.35	17.2	14	24.1	7	7	③ 3-1473562-7
	16.35	13.2	10	20.1	5	6	3-1473562-6
	16.35	13.2	10	20.1	5	5	③ 3-1473562-5
	12.35	9.2	6	16.1	3	4	3-1473562-4
	10.35	7.2	4	14.1	2	3	3-1473562-3
HOLD HSG COLOR	D	C	B	A	N	POS.	PART NUMBER

		DWN S. YOKOZEKI 21 JAN '03		 TE Connectivity			
		CHK D. MITSUGI 30 JAN '03					
DIMENSIONS: 単位: 概 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. MANABE 30 JAN '03		NAME 名称	
		一般公差		PLUG ASSY FOR e-CON - RITS CONN. -			
		0 PLC ± 0.2					
		1 PLC ± 3°					
		2 PLC ±					
3 PLC ±		PRODUCT SPEC		SIZE A3			
4 PLC ±		製品規格					
ANGLES ±		APPLICATION SPEC		DRAWING NO 番号			
		取付適用規格		RESTRICTED TO			
MATERIAL 材料		FINISH 仕上		WEIGHT -		-	
SEE NOTE 		SEE NOTE 		CUSTOMER DRAWING			
				SCALE 尺度		SHEET 3 OF 3	
				4:1		REV C1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1473562-8](#)