


LTR	DESCRIPTION	DATE	DWN	APVD
A1	REV PER ECR-19-008681	04OCT2019	PC	DL

- 1 NO DEFORMING REQUIRED
- 2 LOOSE PIECE TERMINAL MUST MEET ALL APPLICABLE STRIP SPECIFICATIONS IN ADDITION TO THE ABOVE



DIRECTION OFF TOP OF REEL		STOCK THK. .0205 [0,52] x 1.035 WIDE [26,29]			
SURFACE AREA		MATERIAL DESCRIPTION			
WIRE RANGE 3-6 mm ²		A BRASS 100-080 TEMPER 4		151791-5 D2 154897-5	
INS. RANGE 192-234 0.87-5.98		B COPPER		151791-4 D3 154897-4	
SPECIFICATION CLASSIFICATION		C STEEL		151791-3 D 154897-3 OBSOLETE	
CRITICAL ☒		D PHOS BRONZE 100-221 TEMPER 4		151791-2 A2 154897-2	
MAJOR ☒				151791-1 A 154897-1	
MINOR ☐				NUMBER MAT. STRIP BLT M	
REF. (NONE)		PLATING DESCRIPTION		TE Connectivity	
QTY./REEL		1 PRE-TIN		TITLE 315 SURGE FLAG FASION	
LAYOUT NO.		2 ELECTRO-TIN TO 112-16-3 .00008 TO .0004 IN. THK.		REWORKABLE - LOOSE PIECE	
DIE		3 SILVER SDF 63-2A		SCALE 1-1	
TRIMMING BURR NOT TO EXCEED				LOC. A B NO. C-151791 REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[151791-1](#)