




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	0	A2		REVISED PER ECO-12-007964	03MAY2012	KH
		A3		NEW P/N 2-1546111-6 ADDED	17OCT2017	FP

D




1546111-3 AS SHOWN

SEE DETAIL X



32.30	6	2-1546111-6
128.82	25	2-1546111-5
123.74	24	2-1546111-4
118.66	23	2-1546111-3
113.58	22	2-1546111-2
108.50	21	2-1546111-1
103.42	20	2-1546111-0
98.34	19	1-1546111-9
93.26	18	1-1546111-8
88.18	17	1-1546111-7
83.10	16	1-1546111-6
78.02	15	1-1546111-5
72.94	14	1-1546111-4
67.86	13	1-1546111-3
62.78	12	1-1546111-2
57.70	11	1-1546111-1
52.62	10	1-1546111-0
47.54	9	1546111-9
42.46	8	1546111-8
37.38	7	1546111-7
32.30	6	1546111-6
27.22	5	1546111-5
22.14	4	1546111-4
17.06	3	1546111-3
11.98	2	1546111-2
DIM L	NO OF POSN	PART NUMBER

C



- 1 MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: GRAY.
TERMINAL: COPPER ALLOY, TIN PLATED.
2. SUITABLE FOR 1.6-2.4mm PC BOARD THICKNESS.
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC.FILE N° E60677.
- 4 NOT CUMULATIVE TOLERANCE

B



RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S.WELDON 11SEP2002	TE Connectivity		
			CHK C.RICHARD 11SEP2002			
			APVD C.RICHARD 11SEP2002	NAME &DWG_TITLE &DWG_TITLE_2 5.08mm PITCH		
DIMENSIONS: mm			PRODUCT SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C-1546111
			APPLICATION SPEC	RESTRICTED TO -		
MATERIAL 1 -			WEIGHT -	SCALE 5:1		
			CUSTOMER DRAWING	SHEET 1 OF 1		
				REV A3		

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1546111-9](#)