

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

PHYSICAL PROPERTIES:
HOUSING MATERIAL: PBT
FLAMMABILITY: UL94V-0
COLOR: BLACK
MAX BOW/WARP: .0056 IN/IN.

MECHANICAL:
PITCH (TERMINAL SPACING): .563"
WIRE RANGE: 10-22 AWG
RECOMMENDED TIGHTENING TORQUE: 14IN-LBS MAX.

ELECTRICAL PROPERTIES:
MAXIMUM CURRENT: 30A
OPERATING VOLTAGE: 300V

ENVIRONMENTAL PROPERTIES:
OPERATING TEMP RANGE: -40°C TO 120°C

TERMINAL:
TERMINALS: BRASS, TIN PLATED. (UNLESS OTHERWISE STATED)
SCREWS: 8-32 STEEL, NICKEL PLATED. (UNLESS OTHERWISE STATED)
Q.C. TABS: BRASS, NICKEL PLATED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	T5	PART STATUS UPDATED	22JAN2018	RK	PS

△

STAINLESS STEEL SCREWS.

△

WHITE INK STAMP.

△

NICKEL PLATED BRASS TERMINALS.

△

NICKEL PLATED BRASS SCREWS.

△

SEE FIGURE.

△

PRELIMINARY PART NUMBER.

△

OBSOLETE PART NUMBER.

△

TE CONNECTIVITY LOGO LOCATED APPROXIMATE AREA SHOWN.

△/5	-	-	-	-	-	-	-	-	-	-	7.886	8.323	13	1-1546310-3
△/7	-	-	-	-	-	-	-	12	12	12	7.323	7.760	12	4-1546310-8
△	-	8	-	-	-	12	12	12	-	-	7.323	7.760	12	4-1546310-7
△	-	-	-	-	12	12	12	-	-	-	7.323	7.760	12	4-1546310-6
	-	-	-	-	-	-	-	-	-	-	7.323	7.760	12	1-1546310-2
	-	-	-	-	-	-	-	-	-	-	6.760	7.179	11	1-1546310-1
	-	-	-	-	-	-	-	-	-	-	6.197	6.634	10	1-1546310-0
	-	-	-	-	-	-	-	-	-	-	5.634	6.071	9	1546310-9
△/7	-	-	-	-	-	-	-	-	-	8	5.071	5.508	8	4-1546310-5
	-	8	8	-	-	-	-	-	-	-	5.071	5.508	8	2-1546310-9
	-	-	-	-	-	-	-	-	-	-	5.071	5.508	8	1546310-8
△	-	-	-	-	-	7	-	-	-	-	4.508	4.945	7	3-1546310-8
	-	-	-	-	-	-	-	-	-	-	4.508	4.945	7	1546310-7
△/7	-	-	-	-	-	-	-	-	-	6	3.945	4.382	6	4-1546310-4
△/7	-	-	-	-	-	-	-	-	-	-	3.945	4.382	6	4-1546310-3
△	-	-	-	-	-	-	-	-	-	6	3.945	4.382	6	4-1546310-2
△/3/2/1/7	-	-	-	-	-	-	-	-	-	-	3.945	4.382	6	3-1546310-1
	-	-	-	-	-	6	-	-	-	-	3.945	4.382	6	3-1546310-0
	-	6	6	-	-	-	-	-	-	-	3.945	4.382	6	2-1546310-8
△/4/3/7	-	1	1	-	-	5	1	-	-	-	3.945	4.382	6	2-1546310-6
△/7	-	-	-	-	-	-	-	6	-	-	3.945	4.382	6	2-1546310-3
△/7	-	-	-	-	6	-	-	-	-	-	3.945	4.382	6	2-1546310-2
△	-	-	-	-	-	-	-	-	6	6	3.945	4.382	6	2-1546310-1
△/2/7	-	-	-	-	-	-	-	-	6	6	3.945	4.382	6	1546636-1
△/1	-	-	-	6	-	-	-	-	6	-	3.945	4.382	6	1-1546310-9
△	-	-	-	6	-	-	-	-	-	-	3.945	4.382	6	1546589-1
	-	-	-	-	-	-	-	-	-	-	3.945	4.382	6	1546310-6
	-	-	-	-	-	5	-	-	-	-	3.382	3.819	5	3-1546310-7
△/4/3/7	-	1	1	-	-	-	1	-	-	5	3.382	3.819	5	2-1546310-7
	-	-	-	-	-	-	-	-	-	-	3.382	3.819	5	1546310-5
△/6	-	-	-	-	-	-	-	4	4	4	2.819	3.256	4	5-1546310-0
△/4/3/2/7	-	-	-	-	-	-	-	-	-	-	2.819	3.256	4	4-1546310-1
△/4	-	-	-	-	-	-	-	-	-	-	2.819	3.256	4	4-1546310-0
△/3/2/1/7	-	-	-	-	-	-	-	-	-	-	2.819	3.256	4	3-1546310-9
	-	-	-	-	-	-	-	-	-	-	2.819	3.256	4	1546310-4
△/3/7	-	-	-	-	-	-	-	-	-	-	2.256	2.693	3	2-1546310-5
△/1/7	-	-	-	-	-	-	-	3	1	-	2.256	2.693	3	2-1546310-4
△/5/1	-	-	-	1	2	-	-	1	-	-	2.256	2.693	3	2-1546310-0
	-	-	-	-	-	-	-	-	-	-	2.256	2.693	3	1546310-3
	-	-	-	-	-	-	2	-	2	-	1.693	2.130	2	5-1546310-1
	-	-	-	-	-	-	-	-	-	-	1.693	2.130	2	1546310-2
NOTES	9	8	7	6	5	4	3	2	1		DIM B	DIM A	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
-

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
-

DWN
S SCHLEGEL
CHK
S YODER
APVD
S YODER
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

16FEB2007
2/16/07
2/16/07
-
-
-
-

TE Connectivity Ltd.

14.3 (.563) DBL ROW BARRIER STRIP
W/O WASHER
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-1546310







RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 4

REV
T5

1471-9 (1/15)




	—	—	—	—	—	—	2	—	2	—	1.693	2.130		5–1546310–1
	—	—	—	—	—	—	—	—	—	—	10.701	11.138	18	1–1546310–8
	—	—	—	—	—	—	—	—	—	—	10.138	10.575	17	1–1546310–7
	—	—	—	—	—	—	—	—	—	—	9.575	10.012	16	1–1546310–6
	—	—	—	—	—	—	—	—	—	—	9.012	9.449	15	1–1546310–5
  	—	—	—	—	—	—	—	14	14	14	8.449	8.886	14	4–1546310–9
	—	—	—	—	—	—	—	—	—	—	8.449	8.886	14	1–1546310–4
NOTES	(9) OTB JUMPER	(8) .250 QC TAB 90° DOUBLE SIDE	(7) .250 QC TAB 90°/45° DOUBLE SIDE	(6) .250 QC TAB 90° DOUBLE SIDE	(5) .250 QC TAB 45° DOUBLE SIDE	(4) .250 QC TAB STRAIGHT DOUBLE SIDE	(3) .250 QC TAB 90° SINGLE SIDE	(2) .250 QC TAB 45° SINGLE SIDE	(1) .250 QC TAB STRAIGHT SINGLE SIDE	DIM B	DIM A	NO. OF POSN.	PART NUMBER	


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 16FEB2007 CHK S YODER 2/16/07 APVD S YODER 2/16/07		 TE Connectivity Ltd.			
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME 14.3 (.563) DBL ROW BARRIER STRIP W/O WASHER -			
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-		A2	00779	①-1546310	-
CUSTOMER DRAWING						SCALE	REV
						N.TS	2 of 4
							15

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

D




2-1546310-0




2-1546310-6 OBSOLETE


C



OBSOLETE 2-1546310-1



2-1546310-4 OBSOLETE



OBSOLETE 2-1546310-7

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 16FEB2007	 TE Connectivity Ltd.		
DIMENSIONS: INCHES		CHK S YODER 2/16/07			
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD S YODER 2/16/07	NAME 14.3 (.563) DBL ROW BARRIER STRIP W/O WASHER		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC			
MATERIAL		FINISH	SCALE A2	CAGE CODE 00779	DRAWING NO C-1546310
			WEIGHT -	RESTRICTED TO -	
CUSTOMER DRAWING			SCALE NTS	SHEET 3 OF 4	REV T5

D


C

1546310


B

A


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



4-1546310-7 OBSOLETE



5-1546310-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 16FEB2007	 TE Connectivity Ltd.		
DIMENSIONS: INCHES		CHK S YODER 2/16/07			
		APVD S YODER 2/16/07			
		PRODUCT SPEC			
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	NAME 14.3 (.563) DBL ROW BARRIER STRIP W/O WASHER		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		—	SIZE A2	CAGE CODE 00779	DRAWING NO C-1546310
MATERIAL —		FINISH —	WEIGHT —	RESTRICTED TO —	
CUSTOMER DRAWING			SCALE NTS	SHEET 4 OF 4	REV T5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1546310-8](#)