

PHYSICAL PROPERTIES:  
HOUSING MATERIAL: THERMOPLASTIC, PC  
FLAMABILITY: UL94V-0  
COLOR: BLACK


TERMINAL:  
TERMINALS: BRASS, TIN PLATED  
SCREWS: 6-32 STEEL, NICKEL PLATED

MECHANICAL:  
PITCH: .437  
WIRE RANGE: 14-22 AWG  
RECOMMENDED TIGHTENING TORQUE: 12IN-LB

ELECTRICAL PROPERTIES:  
MAX CURRENT: 25A  
OPERATING VOLTAGE: 300V

ENVIRONMENTAL PROPERTIES:  
OPERATING TEMP: -40°C TO 120°C

- 1 SEE FIGURE.
- 2 PRELIMINARY PART NUMBER.
- 3 STAINLESS STEEL SCREWS.
- 4 WHITE INK STAMP.
- 5 TE CONNECTIVITY LOGO LOCATED APPROXIMATE AREA.



	5.646	5.992	12	4-1546670-2
	9.142	9.488	20	2-1546670-0
	8.705	9.051	19	1-1546670-9
2	8.268	8.614	18	3-1546670-0
	8.268	8.614	18	1-1546670-8
	7.831	8.177	17	1-1546670-7
	7.394	7.740	16	1-1546670-6
	6.957	7.303	15	1-1546670-5
	6.520	6.866	14	1-1546670-4
	6.083	6.429	13	1-1546670-3
	5.646	5.992	12	1-1546670-2
	5.209	5.555	11	1-1546670-1
4	4.772	5.118	10	4-1546670-3
2	4.772	5.118	10	3-1546670-8
	4.772	5.118	10	1-1546670-0
2	4.335	4.681	9	3-1546670-5
2	4.335	4.681	9	3-1546670-2
	4.335	4.681	9	1546670-9
1	3.898	4.244	8	4-1546670-1
3	3.898	4.244	8	3-1546670-6
2	3.898	4.244	8	3-1546670-4
2	3.898	4.244	8	3-1546670-3
	3.898	4.244	8	1546670-8
	3.461	3.807	7	1546670-7
1	3.024	3.370	6	3-1546670-1
	3.024	3.370	6	1546670-6
1	2.587	2.933	5	2-1546670-8
1	2.587	2.933	5	2-1546670-7
	2.587	2.933	5	1546670-5
2	2.496	2.933	4	3-1546670-9
1	2.150	2.496	4	2-1546670-9
	2.150	2.496	4	1546670-4
	1.713	2.059	3	1546670-3
	1.276	1.622	2	1546670-2
	DIM B	DIM A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	.01
3 PLC	±	.005
4 PLC	±	-
ANGLES	±	3°
FINISH	-	-

DWN

S SCHEGEL

4/4/03

CHK

C RICHARD

4/4/03

APVD

C RICHARD

4/4/03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

DOUBLE ROW BARRIER STRIP W/ BINDING HD SCREW, .437 SPACING

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=1546670

RESTRICTED TO

-

SCALE

NTS

SHEET


1 of 3

REV


K18

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		—	SEE SHEET 1	—	—	—


DOUBLE SIDED, DOUBLE HOLE  
QC TAB, QTY 5



DOUBLE SIDED, DOUBLE HOLE  
QC TAB, QTY 5




JUMPER, QTY 1





DOUBLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 9



DOUBLE SIDED, DOUBLE HOLE  
90° QC TAB, QTY 9



JUMPER QTY 2



.250  
TYP




2-1546670-7



2-1546670-8

3-1546670-2

DOUBLE SIDED, DOUBLE HOLE  
QC TAB, QTY 5




SINGLE SIDED, SINGLE HOLE  
QC TAB, QTY 2





2-1546670-9

SINGLE SIDED, DOUBLE HOLE  
QC TAB, QTY 6




.250  
TYP



3-1546670-1


DOUBLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 8.

JUMPER, QTY 2




DOUBLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 6

DOUBLE SIDED, DOUBLE HOLE  
90° QC TAB, QTY 4





3-1546670-3

SINGLE SIDED, DOUBLE HOLE  
QC TAB, QTY 18




.250  
TYP






3-1546670-0

DOUBLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 8.



3-1546670-4

11.764	12.110	26	2-1546670-6
11.327	11.673	25	2-1546670-5
10.90	11.236	24	2-1546670-4
10.453	10.799	23	2-1546670-3
10.016	10.362	22	2-1546670-2
9.579	9.925	21	2-1546670-1
9.142	9.488	20	3-1546670-7
DIM B	DIM A	NO OF POS	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S SCHEGEL 4/4/03	 TE Connectivity						
DIMENSIONS: INCHES			CHK C RICHARD 4/4/03							
			APVD C RICHARD 4/4/03	NAME  DOUBLE ROW BARRIER STRIP W/ BINDING HD SCREW, .437 SPACING						
			PRODUCT SPEC  —							
			APPLICATION SPEC  —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
			WEIGHT —	A2	00779	C=1546670	—			
MATERIAL  —			FINISH  —	CUSTOMER DRAWING				SCALE NTS	SHEET 2 of 3	REV K18

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

D


DOUBLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 9.

JUMPER, QTY 1




3-1546670-5

DOUBLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 9




C




SINGLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 10

SINGLE SIDED, DOUBLE HOLE  
90° QC TAB, QTY 10

JUMPER, QTY 4




4-1546670-3




SINGLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 10


B





3-1546670-8




A




4-1546670-1



3-1546670-9



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S	SCHEGEL	4/4/03	 TE Connectivity	
		CHK	C	RICHARD	4/4/03		
		APVD	C	RICHARD	4/4/03	NAME	
		PRODUCT SPEC				DOUBLE ROW BARRIER STRIP W/ BINDING HD SCREW, .437 SPACING	
		APPLICATION SPEC				SIZE	CAGE CODE
		WEIGHT				A2	00779
		CUSTOMER DRAWING				SCALE	NTS
						SHEET	3 OF 3
						REV	K18

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1546670-0](#)