



LOC		DIST		REVISIONS					
FT		0		DESCRIPTION			DATE	DWN	APVD
		P	LTR						
			B1	REVISED PER ECO-10-009455			06MAY2010	HMR	CR





1. ELECTRICAL RATINGS: 300V, 20A
WIRE RANGE: 12-22 AWG
RECOMMENDED TIGHTENING TORQUE: 10 IN LBS
OPERATING TEMPERATURE: 105° MAX

△ TYCO ELECTRONICS LOGO LOCATED IN APPROXIMATE AREA SHOWN

6-32 SEMS SCREW, CAPTIVATED,
STEEL, ZINC PLATED CLEAR CHROMATE



HOUSING
NYLON, BLACK,
UL 94 V-0 RATED



RECOMMENDED PC BOARD LAYOUT

4.875	5.275	16	1-1546734-6
4.550	4.950	15	1-1546734-5
4.225	4.625	14	1-1546734-4
3.900	4.300	13	1-1546734-3
3.575	3.975	12	1-1546734-2
3.250	3.650	11	1-1546734-1
2.925	3.325	10	1-1546734-0
2.600	3.000	9	1546734-9
2.275	2.675	8	1546734-8
1.950	2.350	7	1546734-7
1.625	2.025	6	1546734-6
1.300	1.700	5	1546734-5
.975	1.375	4	1546734-4
.650	1.050	3	1546734-3
.325	.725	2	1546734-2
M	L	NO OF POSN	PART NUMBER

THIS DRAWING IS CONTROLLED THROUGHOUT YOUR ELECTRONIC ORGANIZATION. IT IS SUBJECT TO CHANGE WITHOUT NOTICE AND YOUR ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN S. WELDON 11SEP2003	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK S. YODER 11SEP2003	NAME DUAL BARRIER STRIP ASSEMBLY, .325 PITCH, PCB MOUNT, HIGH RISE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±.1 1 PLC ±0.1 2 PLC ±0.02 3 PLC ±0.005 4 PLC ±0.0005 ANGLES ±.1		APVD S. YODER 11SEP2003	PRODUCT SPEC - APPLICATION SPEC -	
MATERIAL -		WEIGHT -	SIZE A1	CAGE CODE 00779
FINISH -		CUSTOMER DRAWING	DRAWING NO C=1546734	RESTRICTED TO -
		SCALE 4:1	SHEET 1	OF 1
		REV B1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1546734-2](#)