







24	46.2±0.25	51.6	2-1586038-4
22	42.0±0.25	47.4	2-1586038-2
20	37.8±0.25	43.2	2-1586038-0
18	33.6±0.25	39.0	1-1586038-8
16	29.4±0.25	34.8	1-1586038-6
14	25.2±0.25	30.6	1-1586038-4
12	21.0±0.25	26.4	1-1586038-2
10	16.8±0.13	22.2	1-1586038-0
8	12.6±0.13	18.0	1586038-8
6	8.4±0.13	13.8	1586038-6
4	4.2±0.13	9.6	1586038-4
2		5.4	1586038-2
POS	A	B±0.25	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 18-SEP-2002 CHK D. COLEY 18-SEP-2002 APVD D. COLEY 18-SEP-2002		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME WITH DRAIN HOLES VAL-U-LOK(TM) -	
		0 PLC ± 1 PLC ± 0.5 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ±			
MATERIAL 		FINISH 			
		PRODUCT SPEC 108-2112 APPLICATION SPEC 114-13172		SIZE A2	CAGE CODE 00779
		WEIGHT -		DRAWING NO C=1586038	
CUSTOMER DRAWING				SCALE N/A	SHEET 1 of 1
				RESTRICTED TO - REV C6	

1586038

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1586038-4](#)