



- 1 MATERIAL: HOUSING-PA66, UL94V-2 (COLOR-NATURAL, COLOR OF PARTS MAY VARY) CONTACTS-0.25 [.010] THICK BRASS ALLOY.
- 2 CONTACT FINISH: 0.002032 [.000080] MIN BRIGHT TIN OVER 0.000762 [.000030] MIN NICKEL OVER ENTIRE CONTACT.
- 3 MATES WITH VAL-U-LOK(TM) RECEPTACLE HOUSINGS.



24	46.2±0.25	51.6	55.6	2-1586039-4
22	42.0±0.25	47.4	51.4	2-1586039-2
20	37.8±0.25	43.2	47.2	2-1586039-0
18	33.6±0.25	39.0	43.0	1-1586039-8
16	29.4±0.25	34.8	38.8	1-1586039-6
14	25.2±0.25	30.6	34.6	1-1586039-4
12	21.0±0.25	26.4	30.4	1-1586039-2
10	16.8±0.13	22.2	26.2	1-1586039-0
8	12.6±0.13	18.0	22.0	1586039-8
6	8.4±0.13	13.8	17.8	1586039-6
4	4.2±0.13	9.6	13.6	1586039-4
2		5.4	9.4	1586039-2
POS	A	B±0.25	C±0.38	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	
1 PLC	±	0.5
2 PLC	±	0.25
3 PLC	±	-
4 PLC	±	-
ANGLES	±	

FINISH

2

DWN
S. HOOVER
25-SEP-2002

CHK
D. COLEY
25-SEP-2002

APVD
D. COLEY
25-SEP-2002

PRODUCT SPEC
108-2112

APPLICATION SPEC
114-13172

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

VERTICAL HEADER WITH PEGS,
WITH DRAIN HOLES
VAL-U-LOK(TM)

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1586039

RESTRICTED TO
-

SCALE
N/A

SHEET
1 of 1

REV
B5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1586039-6](#)