



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	ECO-13-000550	10JAN2013	DS	AT
	B3	ECO-14-000116	27FEB2014	DS	AT




1 MATERIAL:
TYPE: COPPER ALLOY

2 FINISH:
UNDERPLATE TYPE: NICKEL
TOP PLATE TYPE: TIN

3. PARTS MUST BE FREE OF BURRS, CRACKS, OR OTHER
VISUAL IMPERFECTIONS THAT MAY AFFECT FIT FORM OR FUNCTION

4 NOTE DELETED

5.41	6.10	7.70	SIZE C	1587829-3
4.76	5.41	7.00	SIZE B	1587829-2
4.11	4.76	6.40	SIZE A	1587829-1
MIN	MAX	E	DESCRIPTION	PART NO
WIRE O.D.				

DIMENSIONS: mm		DWN D SIMPSON 01JUN2009		MATERIAL		FINISH	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK A TYLER 01JUN2009		 TE Connectivity			
0 PLC ±- 1 PLC ±0.2 2 PLC ±0.10 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±-		PRODUCT SPEC 108-2394		NAME OUTER FERRULE, HVA280			
		APPLICATION SPEC 114-13259		SIZE A4	CAGE CODE 00779	DRAWING NO C-1587829	RESTRICTED TO -
		WEIGHT -		CUSTOMER DRAWING			
				SCALE 4:1	SHEET 1	OF 1	REV B3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1587829-3](#)