





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		H	UPDATE PER ECO-11-013056	23 JUN 11	CAS	MKS

- 1 CONNECTOR BODY AND JAM NUT MATERIAL: 6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404E
LOCKING RING MATERIAL: BERYLLIUM COPPER, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404E
INSULATOR MATERIAL: LIQUID CRYSTAL POLYMER (LCP) PER ASTM D5138 OR POLYPHENYLENE SULFIDE (PPS) PER ASTM D4067
O-RING MATERIAL: FLUOROSILICONE
- 2 WIRE TERMINATION: 28 AWG SOLID, 30 AWG STRANDED WIRE OR SMALLER
- 3 LUBRICATE O-RING WITH PARKER SUPER-O-LUBE PRIOR TO INSTALLATION
- 4 THIS DRAWING PREVIOUSLY IDENTIFIED AS NANONICS 303-0031

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. STORRY 23 APR 99		 TE Connectivity			
		CHK E. PAULUS 7 MAY 99					
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD S. KAIN 27 JAN 00		NAME	
		0 PLC ± -		PRODUCT SPEC		RECEPTACLE ASSEMBLY, CIRCULAR, PANEL MOUNT, THREADED COUPLING/ QUICK DISCONNECT, METAL, 44 POSITION	
		1 PLC ± -		—			
		2 PLC ± .010		APPLICATION SPEC			
		3 PLC ± .005		—			
		4 PLC ± -				SIZE	
		ANGLES ± 1°				CAGE CODE	
MATERIAL		FINISH		WEIGHT —		DRAWING NO	
SEE NOTES		SEE NOTES		A2		RESTRICTED TO	
				0PJN9		—	
				C=1589062			
				CUSTOMER DRAWING		SCALE 5:1	
						SHEET 1 of 1	
						REV H	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1589062-9](#)