





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		D	REVISED PER ECO-17-012925	20FEB2018	AP	DG

- 1 FOR LOCAL DATA REFER TO YOUR LOCAL TE CONNECTIVITY SALES OFFICE.
- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
- 3 MATERIAL :
HOUSING : THERMOPLASTIC, UL94V-0
BLACK COLOR
CONTACTS : BRASS
SHELL : STEEL
BOARDLOCK : BRASS
SCREW : BRASS
- 4 FINISH :
CONTACT : 0.38µm MIN.GOLD PLATED ON CONTACT AREA
2.54µm MIN. TIN PLATED ON SOLDERTAILS
1.27µm MIN. NICKEL UNDERPLATED OVERALL
SHELL : 2.54 µm MIN NICKEL PLATED.
BOARD LOCK : 1.52µm MIN. TIN PLATED
SCREW : 1.27µm MIN. NICKEL PLATED.
- 5 CHARACTERISTICS
CURRENT RATING : 5A
INSULATION RESISTANCE : 1000MOHMS MIN, 500VDC FOR 2MINS.
TEMPERATURE RATING : -55DEGC ~ +105DEGC
VOLTAGE RATING : 250VDC


6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

INSERT OPTION
(SEE TABLE FOR THREAD)

SCREW LOCK OPTION
(SEE TABLE FOR THREAD)



P.C.B. LAYOUT



6 OBSOLETE	9 WAY D PLUG WITH BOARD LOCKS & 2 x M3-SCREW LOCKS, 0.38µm GOLD, RIGHT ANGLE	4-1634580-2
SUPERSEDED BY 2301843-2	9 WAY D PLUG WITH BOARD LOCKS & 2 x 4-40 SCREW LOCKS, 0.38µm GOLD, RIGHT ANGLE	3-1634580-2
6 OBSOLETE	9 WAY D PLUG WITH BOARD LOCKS & 2 x M3-INSERTS, 0.38µm GOLD, RIGHT ANGLE	2-1634580-2
SUPERSEDED BY 2301843-1	9 WAY D PLUG WITH BOARD LOCKS & 2 x 4-40 INSERTS, 0.38µm GOLD, RIGHT ANGLE	1-1634580-2
DESCRIPTION		PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN J.SANDWELL 15SEP2003

CHK S.EBBUTT 15SEP2003

APVD F.WHEELER-KING 15SEP2003

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

TE Connectivity

NAME
9 WAY D-SUB PLUG WITH BOARD LOCK

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1634580

RESTRICTED TO
-


CUSTOMER DRAWING

SCALE
NTS


SHEET
1 OF 2

REV
D


LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—




- 1 DIMENSION:
 TRAY:L=310,W=220,H=23
 SHIPPING BOX:L=335,W=230,H=320
- 2 QUANTITY:
 90 PCS/TRAY
 13 TRAY/SHIPPING BOX




COVER



TRAY



Tray Layout



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL	15SEP2003	TE Connectivity			
		CHK S.EBBUTT	15SEP2003				
		APVD F.WHEELER-KING	15SEP2003	NAME 9 WAY D-SUB PLUG WITH BOARD LOCK			
		PRODUCT SPEC					
		APPLICATION SPEC					
		WEIGHT		SIZE A3	CAGE CODE 00779	DRAWING NO C-1634580	RESTRICTED TO —
CUSTOMER DRAWING				SCALE NTS	SHEET 2 OF 2	REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1634580-2](#)