



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N1	REDRAW PER ECO-19-001217	11MAR11	RS	DR



AMP WIRE RANGE	 E13288 Listed
22-16 AWG STRANDED	22-16 AWG STRANDED



- △1 STAMP AMP 22-18* APPROX AS SHOWN, 22-16 TERMINALS ARE STAMPED 22-18 IN ACCORDANCE WITH MILITARY SPECIFICATION SAE AS7928, COMMERCIAL WIRE RANGE IS 22-16
- △1 スタンプアンプ22-18 *下図のように約, 22-16端子があります 軍事仕様に従って22-18の刻印 SAE AS7928、商用配線範囲は22-16です

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm ² [509-3,260] CIR MILS STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI.S 07MAY2019	 TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK ROHDE DANIEL F 07MAY2019			
		APVD ROHDE DANIEL F 07MAY2019	NAME TERMINAL, RING TONGUE, SOLISTRAND ターミナル、リングトング、ソリストランド		
		PRODUCT SPEC UL 486 A-B	22-16 AWG		
MATERIAL COPPER PER (銅当たり) ASTM B-152 ANNEALED (焼なまし)		FINISH TIN PLATE (ティンプレート) 0.00254[.000100] MIN	SIZE A2	CAGE CODE 00779	DRAWING NO C-170720
CUSTOMER DRAWING			WEIGHT	RESTRICTED TO	—
			SCALE 10:1	SHEET 1 of 1	REV N1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[170720-1](#)