






- 注 ;
1. 適用電線範囲 : AWG #28~26 (UL1571,UL1061)
被覆外径 : 0.83~1.05
(但し、使用電線について適合性に確認が必要です。)
 2. 材料 : ハウジング : ガラス入りP.B.T UL94V-0
コンタクト : 錫めつき済磷青銅
 3. 適用製品規格番号 : 108-5217
 4. 取付適用規格番号 : 114-5103
- NOTES;
1. APPLICABLE WIRE SIZE : AWG #28~26 (UL1571,UL1061)
INSULATION DIA RANGE : 0.83~1.05
 2. MATERIAL :
HOUSING : P.B.T. (G.F)UL94V-0
CONTACT : PRE-TIN PHOS BRONZE
 3. PRODUCT SPEC : 108-5217
 4. APPLICATION SPEC : 114-5103

3-173983-5	15	28	32
3-	-4	14	26
3-	-3	13	24
3-	-2	12	22
3-	-1	11	20
3-	-0	10	18
2-	-9	9	16
2-	-8	8	14
2-	-7	7	12
2-	-6	6	10
2-	-5	5	8
2-	-4	4	6
2-	-3	3	AS SHOWN
2-173983-2	2	AS SHOWN	
CREAM YELLOW クリームイエロー	Pos. 極数	G	H
PART No. 製品型番			



F1	REVISED PER ECO-11-005294	RK	HMR	09APR 11
LTR	変更 (REVISION RECORD)	DR	CHK	DATE

適合電線範囲 (WIRE RANGE)	被覆外径 (INSULATION DIA.)	名称 (NAME)
NOTE 1 mm ² (AWG -)	NOTE 1 mmφ	CT AMP-IN HEADER 2mm PITCH MT HORIZONTAL (H-TYPE)
材料 (MATERIAL)	仕上 (FINISH)	
NOTE 2	---	
DR. 23/AUG/'99 J. TSUJI	DE. 23/AUG/'99 J. TSUJI	
APP. 25/AUG/'99 J. TSUJI	APP. 25/AUG/'99 J. TSUJI	

TE Connectivity	
一般公差 (GENERAL TOLERANCE)	LOC 番号 (No.)
10以下 : ±0.2 10~30以下 : ±0.25 30~100以下 : ±0.3 100以上 : ±0.5	B J C-173983
尺度 (SCALE)	REV. SHEET
5-1	F1 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-173983-2](#)