

注記
NOTE

NOTE


1 嵌合相手製品型番及び、嵌合時寸法は表-1参照のこと。

1 MATING COUNTER PART NUMBER AND DIMENSIONS AFTER MATING: SEE TABLE 1.



HEADER HOUSING
ヘッダーハウジング
④ (PPS UL94V-0)

SECT A-A



嵌合時寸法:巾(mm)x高さ(mm)

DIMENSIONS AFTER MATING : WIDTH(mm) x HEIGHT(mm)



嵌合相手側 MATING COUNTER コネクタ CONN		POST HDR ASSY		SMT TYPE-IMPROVED TYPE			
		RECE HDR ASSY		X-176756-X			
				ボス付 吸着テープ付 WITH BOSS, WITH POLYIMIDE TAPE			
				ハウジング 高さ 寸法 HOUSING HEIGHT C DIMENSIONS			
		6.85		9.35			
DIP TYPE	V TYPE		5.6(巾W)x		7.0(巾W)x		
	X-174635-X		8.0(高H)		10.5(高H)		
	H TYPE		5.6(巾W)x		7.0(巾W)x		
	X-174636-X		8.8(高H)		11.3(高H)		
SMT TYPE	V TYPE		5.6(巾W)x		7.0(巾W)x		
	ボス無 WITHOUT BOSS		X-174904-X		7.0(巾W)x		
	ボス付 WITH BOSS		X-174639-X		8.0(高H)		
					10.5(高H)		
		H TYPE		5.6(巾W)x		7.0(巾W)x	
		ボス無 WITHOUT BOSS		X-174905-X		9.9(高H)	
		ボス付 WITH BOSS		X-174640-X		12.4(高H)	

TABLE 1
表—1

SMT TYPEは、巾及び高さ寸法に
SMT TYPE INCLUDE DIMENSIONS
半田付タイン部寸法を含みます。
OF SOLDER DIP TINE.

嵌合狀態

CONCLUSION

[illegible]

P.C.B MOUNTING LAYOUT 基板加工寸法

適用基板厚：0.6mm最小)
(APPLICABLE P.C.B THK : 0.6mm MIN)

THIS DRAWING IS A CONTROL DOCUMENT

DIMENSIONS:
單位：耗

TOLERANCES UNLESS OTHERWISE SPECIFIED

MATERIAL
材料

3

$\triangle 2$ 一般公差

10以下：±0.2
10を越え 30以下：±0.25
30を越え 100以下：±0.3

③ 仕上げ：ニッケル下地錫めっき

2 GENERAL TOLERANCE

~~$$10 \geq \pm 0.25$$

$$30 \geq \pm 0.25$$

$$100 \geq \pm 0.25$$~~

5 OBSOLETE PARTS: OBSOLETE STREAMLINING
REFER TO REMOVAL DISINIS

[illegible]

TE Connectivity

1.25 F-P CONNECTOR (B-TO-B)
DOUBLE ROW POST HDR ASSY SMT TYPE
WITH BOSS

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-176756	—

CUSTOMER DRAWING

SCALE
尺度

SHE

1 OF 1

EV D2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-176756-2](#)