

C-179608

NUMBER



METRIC

単位: 寸法 DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST

AMP-J
REV. 10/93

2-179608-4 : 本 ☒


2-179608-4 : AS SHOWN

注 記


1. 適用コネクタ型番 : X-173977-X (リセ)

NOTE


1. CONNECTOR P/N : X-173977-X (REC)






26P, 20P



28P, 22P, 16P



30P, 24P, 18P



34.3	28.0	14	30	3-179608-0
32.3	26.0	13	28	2- -8
30.3	24.0	12	26	2- -6
28.3	22.0	11	24	2- -4
26.3	20.0	10	22	2- -2
24.3	18.0	9	20	2- -0
22.3	16.0	8	18	1- -8
20.3	14.0	7	16	1-179608-6
A	B	N	P05 極数	型番 P/N

Copyright ©1990年

日本エー・エム・ピー株式会社

Copyright ©1990

AMP (Japan), LTD.
ALL RIGHTS RESERVED.

AMP

日本エー・エム・ピー株式会社
Kasawaki, Japan

A2	ECR-16-008796	T.Q	W.H	7/19/96	電線範囲 (WIRE RANGE)	被覆外径 (INSULATION DIA.)	名称 (NAME)	CT ダブルローコネクタ用ホルダー (タイプ: CT MT 用)	
AI	REVISED				— # mm² (AWG — #) —	— # mmφ —		HOLDER FOR CT DOUBLE ROW CONN. (TYPE: CT MT TYPE)	
A	REVISED	FJ00-4832-94	H.S.T.F	7/25/96	材料 (MATERIAL)	色 (COLOR)	一般公差 (GENERAL TOLERANCE)	SIZE	LOC
O	RELEASED	FJ00-0588-94	T.F.S.K	5/18/94	66NYLON	NATURAL	10以下: ±0.2	B	J
LTR	変更 (REVISION RECORD)		DR	CHK	66ナイロン樹脂	自然色	10を超え30以下: ±0.25	番号 (No.)	
					OR. 5/17 '96	DE. 5/17 '96	30を超え100以下: ±0.3	C-179608	
					CHK. 5/17 '96	APP. 5/17 '96	角 度: ±3°	尺度 (SCALE)	REV.
					S.KUBOUCHI	T.FURUYA		— # —	A2
									SHEET
									1 OF 1

(CUSTOMER DRAWING)

参 考 図 面

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-179608-4](#)