





- △ MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- △ 2 FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
- △ 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE AND STANDARD IN APPROXIMATE AREA SHOWN
- △ 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
5. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT, TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- △ 6 REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- △ 7 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIAMATE AREA.


CONTACT LAYOUT

A = 4.50mm (DIM M)

B = 3.70mm (DIM M)


G = GROUND 6.00mm

ROWS	COLUMNS								
		8	7	6	5	4	3	2	1
	A	G	A	G	A	G	A	G	B
	B	A	A	A	A	A	A	A	B
	C	A	G	A	G	A	G	A	G
	D	G	A	G	A	G	A	G	A
	E	A	A	A	A	A	A	A	A
	F	A	G	A	G	A	G	A	G
	G	G	A	G	A	G	A	G	A
	H	A	A	A	A	A	A	A	A
	I	A	G	A	G	A	G	A	G
	J	G	A	G	A	G	A	G	A
	K	A	A	A	A	A	A	A	A
	L	A	G	A	G	A	G	A	G
	M	G	A	G	A	G	A	G	A
	N	A	A	A	A	A	A	A	A
	O	A	G	A	G	A	G	A	G



○ = SIGNAL
⊗ = GROUND

RECOMMENDED PC BOARD LAYOUT BACKPLANE, COMPONENT SIDE SHOWN
SCALE 6:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN B. CARBO 06APR2009	2065799-1	
DIMENSIONS:		CHK R. PATTERSON 06APR2009	PART NUMBER	
mm		APVD R. PATTERSON 06APR2009	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	HEADER ASSEMBLY, OPEN ENDED, 5 PAIR, 8 COLUMN, SHORT PIN SELECT LOAD, NOTCHED WALL	
0 PLC ±		APPLICATION SPEC	SIZE	
1 PLC ±		WEIGHT	CAGE CODE	
2 PLC ±		CUSTOMER DRAWING	DRAWING NO	
3 PLC ±		SCALE 2:1	SHEET 1 OF 1	
4 PLC ±		REV D	RESTRICTED TO	
ANGLES ±				
FINISH				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2065799-1](#)