








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	Y	REV PER ECO 19-019228	4-17-20	CT	DM



- 1. CONTACTS INCLUDED IN ASSEMBLY.
- MATL: STEEL, PER ASTM-A-109.
- FINISH: CADMIUM PER QQ-P-416.
- MATL: BRASS PER ASTM-B-36.
- FINISH: PLATED ZINC .00020 MIN THK PER ASTM-B-633. YELLOW CHROMATE FINISH.
- CONTACT
- BODY MAT'L: BERYLLIUM COPPER PER ASTM-B-197.
- BODY FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER NICKEL, .000050 MIN THK PER QQ-N-290.
- HOOD MAT'L: STAINLESS STEEL PER ASTM-A-240.
- HOOD FINISH: PASSIVATED PER QQ-P-35
- FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER FLASH
- FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER, .000100 MIN THK PER MIL-C-14550.
- CONTACT
- BODY MAT'L: BERYLLIUM COPPER PER ASTM-B-197.
- BODY FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER, .000100 MIN THK PER MIL-C-14550.
- HOOD MAT'L: COPPER ALLOY PER QQ-B-613.
- FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER, .000100 MIN THK PER MIL-C-14550.



OBSOLETE				4U884 SOCN R10002677-0111	211015-6
				2A091-006W-001	211015-5
				—	211015-4
				—	211015-3
				(1J02-111)	211015-2
				—	211015-1
	EYELET	SHELLS	CONTACT	CUSTOMER P/N	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 11-3-98	 TE Connectivity			
DIMENSIONS: INCHES		CHK J.NORTON 11-17-98				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J.NORTON 11-17-98	NAME	CONNECTOR SAVER,AMPLIMITE 104 POSN.,SIZE 6,SERIES 90 —		
	0 PLC ± —	PRODUCT SPEC				
	1 PLC ± —	APPLICATION SPEC				
	2 PLC ± —					
	3 PLC ± .005 [0.13]		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	4 PLC ± —					
MATERIAL —	FINISH —	WEIGHT 0.000000	A1	00779	C211015	—
CUSTOMER DRAWING			SCALE 4:1 SHEET 1 OF 1 REV Y			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[211015-5](#)